

DESCRIPTION

694 Series LEDTrims - 6-inch Aperture Directional Eyeballs with Baffle - are integral elements in the Halo ML56 LED Downlighting System. ML56 LED System is a series of modular LED Light Modules for use with dedicated 5" or 6" ML56 LED trims. The ML56 LED trims in 5" and 6" aperture sizes are designed to fit Halo, All-Pro and others 5" or 6" recessed housings. The ML56 system is suitable for new construction, remodel or retrofit installation.

Catalog #	Туре
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

694 Series LED trims are 6-inch aperture Eyeballs with baffles offered in White (Matte White), Satin Nickel, and Tuscan Bronze. The precision spun aluminum eyeball with baffle element delivers the functionality of a directional accent. The directional eyeball can be tilted from 0 to 30 degrees, and the rotational mechanism allows for rotation adjustment up to 360 degrees. The 694 eyeballs may be used in most standard height 6-inch aperture recessed housings; Halo, All-Pro, and more* (refer to ML56 LED Light Module specifications for details).

- For use with ML56 Series LED light modules
- Eyeball with baffle and self- flange
- · Torsion springs pull trim and light module tight to ceiling
- For use in standard or shallow housings
- Eyeball tilts from 0 to 30 degrees
- · Rotation adjustment mechanism for rotation capbility up to 360 degrees
- Damp location listed with ML56 LED light modules

Compatible with ML56 LED System of LED Downlight Light Modules

600 Series - 80CRI, 600lm 5"/6" LED Retrofit Downlight Engine

ML5606827 - 2700K ML5606830 - 3000K ML5606835 - 3500K ML5606840 - 4000K

900 Series - 80CRI, 900Im


5"/6" LED Retrofit Downlight Engine

ML5609827 - 2700K ML5609830 - 3000K ML5609835 - 3500K ML5609840 - 4000K

1200 Series - 80CRI, 1200lm

5"/6" LED Retrofit Downlight Engine

ML5612827 - 2700K ML5612830 - 3000K ML5612835 - 3500K ML5612840 - 4000K



600 Series - 90CRI, 600lm

5"/6" LED Retrofit Downlight Engine

ML5606927 - 2700K ML5606930 - 3000K ML5606935 - 3500K ML5606940 - 4000K

900 Series - 90CRI, 900lm

5"/6" LED Retrofit Downlight Engine

ML5609927 - 2700K ML5609930 - 3000K ML5609935 - 3500K ML5609940 - 4000K

1200 Series - 90CRI, 1200lm

Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269

P: 770-486-4800 www.cooperlighting.com

5"/6" LED Retrofit Downlight Engine

ML5612927 - 2700K ML5612930 - 3000K ML5612935 - 3500K ML5612940 - 4000K



694WB



694SNB



694TBZB

694 Series **LED Trim**

6-Inch Eveball with Baffle

For use with **Halo ML56 LED System Light Modules**

ORDERING INFORMATION

SAMPLE NUMBER: 694WB

OAM EE NOMBELL COANS		
Trim	Finish	Accessory
694 = 6" Eyeball with Baffle	WB=White Eyeball with Baffle, White Flange SNB=Satin Nickel Eyeball with Baffle, Satin Nickel Flange TBZB=Tuscan Bronze Eyeball with Baffle, Tuscan Bronze Flange	TRM690WH=6" LED Oversize Trim Ring for use with 69* series trims, White 6.9" I.D., 9.5" O.D. Ring slips over LED trim. Inset design allows 6" trim to fit into oversize ring for an even trim surface

^{* 694} trims are for torsion spring installation only. Not for use with ML56CLIP 6" friction clip mounting. Use ML7RAB retrofit adapter band as an alternative to ML56CLIP with 694 trims.

