



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



702212HDG Cond Clamp

Thomas&Betts-Abb Ins Prod

| | |
|------------------|---------------------------|
| Catalog Number | 702212HDG |
| Manufacturer | Thomas&Betts-Abb Ins Prod |
| Description | |
| Weight per unit | 0.3800 (lbs/each) |
| Product Category | Channel & Strut Fittings |

Features

| | |
|----------|----------|
| Material | Steel IN |
|----------|----------|

Dimensions and Weight

| | |
|------|--------------|
| Size | 2-1/2 Inches |
|------|--------------|

Descriptions

| | |
|------------------|--|
| Description | COND CLAMP |
| Product Type | RGD Cond CLP 2-1/2IN 12GA HDG STL |
| Special Features | Bolt head is combination slot and hex head for flexibility of attachment |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Superstrut |
| GTIN | 00616013140758 |
| Manufacturers Part Number | 702 2 1/2 HDG |
| UPC | 616013140758 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | STRUT STRAPS |
| Type | Pipe Straps, Pipe Clamps & Hangers (Series 700) |

Packaging

| | |
|-----------------|------|
| Carton | 50 |
| Weight Per each | 0.38 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel. |
|-------------|---|

Superstrut[®]

Pipe Straps, Pipe Clamps & Hangers (Series 700)

T&B Catalog Number:

702 2 1/2 HDG

UPC Number:

61601314075

Status:

Active

Description:

Strap, 12 Gauge, Size 2-1/2 Inch, Outer Diameter Size 2.875 Inches, Hot-Dip Galvanized Steel, For Rigid or IMC Conduit, Pipe and Electrical Metal Tubing

Features

Bolt head is combination slot and hex head for flexibility of attachment

Square nut is captivated on the shoulder for easy one-handed tightening.

Straps are interchangeable with 1-1/2 in. strut, for broader application.

Straps are shipped assembled so counting and sorting are easier.

Pipe and conduit sizes are shown on the strap for easy identification.

Application

Superstrut Pipe Straps are designed to be twist inserted anywhere along the slot side of the channel.

General

| | |
|---------------------|--------------------|
| Trade Size (inches) | 2 1/2 |
| Material | Steel |
| Finish | Hot-Dip Galvanized |
| Design Load (lbs) | 1000 |
| Safety Factor | 3 |

Dimension Information

| | |
|-----------------------------|-------|
| Rigid Conduit Size (inches) | 2 1/2 |
| Material Thickness (ga.) | 12 |
| Outside Diameter (inches) | 2.875 |

Packaging



| | |
|--------------------|-------------------|
| Package in Units | 50 |
| T&B Sold in UOM | Each |
| T&B Weight Per UOM | 37.5 lbs. per 100 |

Application Support

| | |
|------------------------------------|----------------------|
| Metal Framing Channels-Series 1000 | Available on Website |
| Finishes | Available on Website |
| Pipes-Clamps & Hangers-Series 700 | Available on Website |

Certifications

| | |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.

T&B Technical Support
MS 3B-50

Hours: 7AM - 6PM CDT
Monday-Friday

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com