

# Carlton®

## Outlet Boxes

### T&B Catalog Number:

7074-02-BH

### UPC Number:

78635852850

### Status:

Active

### Description:

4-gang 48 cu.in. brown phenolic outlet box with side bracket, stabilizing bar and #36 clamps bulk packed.

### Features

#36 clamps bulk packed

### Application

Can be installed in the same stud cavity of a shared two-hour wall.

Phenolic boxes may also face opposite directions with only a 3 in. horizontal separation, ideal for multi-family construction.

All phenolic boxes are permissible for use with 90 degree C connectors.

Listed for masonry walls

### General

Material	Non-Metallic
Color	Brown
Wiring System	Non-metallic sheathed cable
Volume (cu.in.)	48
Work	New
Mounting Method	Side bracket and stabilizing bar
Number of Gangs	Four

### Dimension Information

Length (inches)	3 5/16
Width (inches)	7 5/8
Depth (inches)	2 5/8

### Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	103.5 lbs. per 100

### Application Support

Product Overview-Carlton Brown PH Box- Available on Websites

### Certifications



File Nbr:


E 11461

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.

T&B Technical Support  
MS 3B-50

Hours: 7AM - 6PM CDT  
Monday-Friday



Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)

# Carlton®

## Outlet Boxes

### T&B Catalog Number:

7074-02-BH

### UPC Number:

78635852850

### Status:

Active

### Description:

4-gang 48 cu.in. brown phenolic outlet box with side bracket, stabilizing bar and #36 clamps bulk packed.

### Features

#36 clamps bulk packed

### Application

Can be installed in the same stud cavity of a shared two-hour wall.

Phenolic boxes may also face opposite directions with only a 3 in. horizontal separation, ideal for multi-family construction.

All phenolic boxes are permissible for use with 90 degree C connectors.

Listed for masonry walls

### General

Material	Non-Metallic
Color	Brown
Wiring System	Non-metallic sheathed cable
Volume (cu.in.)	48
Work	New
Mounting Method	Side bracket and stabilizing bar
Number of Gangs	Four

### Dimension Information

Length (inches)	3 5/16
Width (inches)	7 5/8
Depth (inches)	2 5/8

### Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	103.5 lbs. per 100

### Application Support

Product Overview-Carlton Brown PH Box- Available on Websites

### Certifications



File Nbr:


E 11461

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.

T&B Technical Support  
MS 3B-50

Hours: 7AM - 6PM CDT  
Monday-Friday



Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)