



Core & Coil (71A) MH ~GT~ 450W

CORE & COIL HID MH BAL 1500W M48 480V KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information					
ANSI Code	M48				
Lamp Type	1500W MH				
Number of Lamps	1 piece/unit				
Circuit Type	CWA				
Ballast Type	Magnetic HID				
Base Model	71A6742A				
Core Size	4 1/4 x 6				
Suitable For Outdoor Use	Yes				
Ignitor Catalog Number	NA				
Ignitor Temperature Rating	NA				
Capacitor Value	32 MFD				
Capacitor Catalog Number	MD3202100				
Capacitor Requirements	525V				
Capacitor Temperature Rating	90°C				
Capacitor Diameter/Oval Dimensions	2 in				
Capacitor Height	3.75 in				
Automatic Restart	No				
Operating and Electrical					
Input Voltage	480 V				

Input Frequency	60 Hz			
Input Current (Open Circuit)	1.56 A			
Input Current (Starting)	2.94 A			
Input Current (Short Circuit)	2.41-3.62 V			
Secondary Short Circuit Current	7.4-9 A			
Constant Wattage Deviation	12%			
Ballast Factor (Nom)	1			
Power Factor (Nom)	0.90			
Open Circuit Voltage	460 V			
Input Current (Nom)	3.43 A A			
Input Power (Nom)	1610 W			
Rated Lamp Power	1500 W			
Wiring				
Wire Striplength	0.5 mm			
Wire Length by Color	12"			
Wire Type	Stranded			
Remote Wiring Configuration Allowed	Yes			
Max Ballast-Lamp Distance Remote Wiring Determined by AWG used				
Recommended Fuse Value	10 A			


Datasheet, 2019, March 22 data subject to change

Core & Coil (71A) MH ~GT~ 450W

Approval and Application					
Open Circuit Voltage Test (Volts)	414-506 V				
Approval Marks	ULR CSA certificate RoHS Compliant				
Temperature Marking	E				
UL Recognized	Yes				
Hipot Test (1 Minute)	2000 V				
Hipot Test (2 Seconds)	2500 V				
UL Insulation Class	H(180°C)				
UL Temperature Code	1029E				
Product Data					
Order product name	CORE & COIL HID MH BAL 1500W M48				
	480V KIT				

EAN/UPC - Product	781087674215
Order code	913700536909
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700536909
Net Weight (Piece)	14.438 kg

Dimensional drawing



MH BAL 1500W M48 480V KIT

Product	C1	C2	A1	A2	А3	B1	B2
CORE & COIL HID MH BAL 1500W	6.7 in	4.7 in	6 in	5.4 in	4.4 in	4.3 in	3.9 in
M48 480V KIT							

