



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10070 E. 40th Ave.
80238-0000, CO Denver
Phone: 720-259-9108
Fax: 720-259-9109



71333C 36W/48W/60W 3K/4K/5K Barn Light With Short Cap *Morris Products Inc.*

Catalog Number	71333C
Manufacturer	Morris Products Inc.
Description	Led Area Light Fixture, Powder Coated Gray Finish; UL (Canada and Us), DLC Approval; Bracket Mounting; Led Lamp Type; 50 Watt Lamp Wattage; Die-Cast Aluminum Housing Material; 120/208/240/277 Volt Ac Lamp/Ballast Voltage
Weight per unit	7.5 (lbs/each)
Product Category	Led Roadway Lighting

Features

Control Type	Twist Lock Photocell
Lamp Type	LED
Lamp Wattage	50 Watt
Lamp/Ballast Voltage	120/208/240/277 Volt AC
Refractor/Lens Type	Anti-Glare Polycarbonate Frosted Lens

Material, Color, and Finish

Finish	Powder Coated Gray
Housing Material	Die-Cast Aluminum



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10070 E. 40th Ave.
80238-0000, CO Denver
Phone: 720-259-9108
Fax: 720-259-9109

Descriptions

Additional Information	Hardware Material Stainless Steel; Enclosure Rating IP65; Current Rating 0.6 Amp; Overall Dimension 21-1/4 Inch Depth x 24 Inch Height; Intensity 5050 Lumen; Efficacy Rating 101 Lumen per Watt; Color Rendering Index 72; Color Temperature Rating 5000 Kelvi
Commodity Description	Led Roadway Lighting
Description	36W/48W/60W 3K/4K/5K BARN LIGHT WITH SHORT CAP
extra long description	POWDER COATED GRAY FINISH; UL (CANADA AND US), DLC APPROVAL; BRACKET MOUNTING; LED LAMP TYPE; 50 WATT LAMP WATTAGE; DIE-CAST ALUMINUM HOUSING MATERIAL; 120/208/240/277 VOLT AC LAMP/BALLAST VOLTAGE; TWIST LOCK PHOTOCELL CONTROL TYPE; ANTI-GLARE POLYCARBONATE FROSTED LENS REFRACTOR/LENS TYPE; HARDWARE MATERIAL STAINLESS STEEL; ENCLOSURE RATING IP65; CURRENT RATING 0.6 AMP; OVERALL DIMENSION 21-1/4 INCH DEPTH X 24 INCH HEIGHT; INTENSITY 5050 LUMEN; EFFICACY RATING 101 LUMEN PER WATT; COLOR RENDERING INDEX 72;
Long Description	LED AREA LIGHT FIXTURE, POWDER COATED GRAY FINISH; UL (CANADA AND US), DLC APPROVAL; BRACKET MOUNTING; LED LAMP TYPE; 50 WATT LAMP WATTAGE; DIE-CAST ALUMINUM HOUSING MATERIAL; 120/208/240/277 VOLT AC LAMP/BALLAST VOLTAGE
Product Type	Led Area Light Fixture

Manufacturer Information

Brand	Morris Products Inc.
GTIN	00601986713337
Manufacturers Part Number	71333C
UPC	601986713337

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

Packaging

Carton	1
Weight Per each	7.5

Uses, Certifications, and Standards

Approval	UL (Canada and US), DLC
Mounting	BRACKET