

# Plenum Electronic Wire

## Plenum Unshielded Electronic Wire

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
72302	22/2 stranded BC (7/30)	22	2	CMP CL3P	10 lbs	0.109"	1,000' Box (46)	Natural (23)
72304	22/4 stranded BC (7/30)	22	4	CMP CL3P	15 lbs	0.127"	1,000' Box (46)	Natural (23)
72306	22/6 stranded BC (7/30)	22	6	CMP CL3P	22 lbs	0.150"	1,000' Box (46)	Natural (23)
72308	22/8 stranded BC (7/30)	22	8	CMP CL3P	27 lbs	0.163"	1,000' Reel (06)	Natural (23)
72310	22/10 stranded BC (7/30)	22	10	CMP CL3P	37 lbs	0.198"	1,000' Reel (06)	Natural (23)
72312	22/12 stranded BC (7/30)	22	12	CMP CL3P	43 lbs	0.203"	1,000' Reel (06)	Natural (23)
71902	18/2 stranded BC (7/0.0152)	18	2	CMP CL3P	20 lbs	0.142"	1,000' Reel (06) 1,000' Box (46)	Natural (23)
71903	18/3 stranded BC (7/0.0152)	18	3	CMP CL3P	25 lbs	0.151"	1,000' Reel (06) 1,000' Box (46)	Natural (23)
71904	18/4 stranded BC (7/0.0152)	18	4	CMP CL3P	33 lbs	0.166"	1,000' Reel (06) 1,000' Box (46)	Natural (23)
71906	18/6 stranded BC (7/0.0152)	18	6	CMP CL3P	48 lbs	0.205"	1,000' Reel (06)	Natural (23)
71908	18/8 stranded BC (7/0.0152)	18	8	CMP CL3P	61 lbs	0.223"	1,000' Reel (06)	Natural (23)
71910	18/10 stranded BC (7/0.0152)	18	10	CMP CL3P	75 lbs	0.262"	1,000' Reel (06)	Natural (23)
71912	18/12 stranded BC (7/0.0152)	18	12	CMP CL3P	88 lbs	0.271"	1,000' Reel (06)	Natural (23)
71702	16/2 stranded BC (19/0.0117)	16	2	CMP CL3P	27 lbs	0.177"	1,000' Reel (06)	Natural (23)
71703	16/3 stranded BC (19/0.0117)	16	3	CMP CL3P	37 lbs	0.195"	1,000' Reel (06)	Natural (23)
71704	16/4 stranded BC (19/0.0117)	16	4	CMP CL3P	51 lbs	0.214"	1,000' Reel (06)	Natural (23)
71502	14/2 stranded BC (19/0.0147)	14	2	CMP CL3P	41 lbs	0.206"	1,000' Reel (06)	Natural (23)



71902



71904

# Packaging Options

Coleman Cable offers four types of packaging options.


- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

\* Not all options are available for each product



## Coleman Cable Part Legend



Put-ups	Code	Colors	Code		Code
Reel, 250 ft	04	White	01	Pink	11
Reel, 500 ft	05	Yellow	02	Purple	13
Reel, 1,000 ft	06	Orange	03	Clear	18
Reel-in-box, 1,000 ft	16	Red	04	Fluorescent	
RabbitPull™ Pull-Box, 500 ft	45	Green	05	Pink	21
RabbitPull™ Pull-Box, 1,000 ft	46	Blue	06	Ivory	22
SignaCoil™ 500 ft	55	Brown	07	Natural	23
SignaCoil™ 1,000 ft	56	Black	08	Beige	33
		Gray	09	Red Striped	
				CorraClad™	44

