



# Core & Coil (71A) MH 175W - 450W

## CORE & COIL HID MH BAL 400W M59 5-TAP KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

### Product data

General Information		Electrical	
ANSI Code	M59	Input Frequency	60 Hz
Lamp Type	400W MH	Input Current (Open Circuit)	2.86/1.45/1.29/1.1/0.62 A
Number of Lamps	1 piece/unit	Input Current (Starting)	3.51/2.0/1.72/1.49/0.86 A
Circuit Type	CWA	Input Current (Short Circuit)	2.7-4.05/1.56-2.34/1.29-1.92/1.17-1.76/0.68-1.02 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	3.04-4.56 A
Base Model	71A6051	Constant Wattage Deviation	10%
Core Size	4 1/4 x 4 3/4 (2 coil)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	NA	Open Circuit Voltage	300 V
Ignitor Temperature Rating	NA	Input Current (Nom)	4.13/2.29/2.2/1.72/0.99 A A
Capacitor Value	24 MFD	Input Power (Nom)	455 W
Capacitor Catalog Number	7C240P40R	Rated Lamp Power	400 W
Capacitor Requirements	400V	<b>Wiring</b>	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.75 in	Wire Length by Color	12"
Capacitor Height	4.8 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
<b>Operating and Electrical</b>		Max Ballast-Lamp Distance Remote	Determined by AWG used
Input Voltage	120/208/240/277/480 V	Wiring	


## Core & Coil (71A) MH 175W - 450W

Recommended Fuse Value	10/7/5/5/3 A
<b>Approval and Application</b>	
Open Circuit Voltage Test (Volts)	280-320 V
Approval Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	C/C/D/C/D
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029D

### Product Data

Order product name	CORE & COIL HID MH BAL 400W M59 5-TAP KIT
EAN/UPC - Product	781087110379
Order code	913710414201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913710414201
Net Weight (Piece)	5.938 kg

### Dimensional drawing



Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID MH BAL 400W M59 5-TAP KIT	4.45 in	2.34 in	4.8 in	4.4 in	4.3 in	3.9 in

MH BAL 400W M59 5-TAP KIT

