PHILIPS Lighting



Core & Coil (71A) HPS 200W - 400W

CORE & COIL HID HPS BAL 400W S51 480V/120T KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information	
ANSI Code	S51-M169
Lamp Type	400W HPS
Number of Lamps	1 piece/unit
Circuit Type	CWA
Ballast Type	Magnetic HID
Base Model	71A8443TA
Core Size	4 x 4 (2 coil)
Suitable For Outdoor Use	Yes
Ignitor Catalog Number	LI501-H4
Ignitor Temperature Rating	105°C
Capacitor Value	55 MFD
Capacitor Catalog Number	7C550P24RA
Capacitor Requirements	240V
Capacitor Temperature Rating	105°C
Capacitor Diameter/Oval Dimensions	1.85 in
Capacitor Height	3.7 in
Automatic Restart	No


Operating and Electrical				
Input Voltage	480/120T V			
Input Frequency	60 Hz			
Input Current (Open Circuit)	0.55 A			
Input Current (Starting)	0.75 A			
Input Current (Short Circuit)	0.5-0.8 A			
Secondary Short Circuit Current	6-7.4 A			
Constant Wattage Deviation	Within Trapezoid			
Ballast Factor (Nom)	1			
Power Factor (Nom)	0.90			
Open Circuit Voltage	190 V			
Input Current (Nom)	0.97 A A			
Input Power (Nom)	464 W			
Rated Lamp Power	400 W			
Wiring				
Wire Striplength	0.5 mm			
Wire Length by Color	12"			
Wire Type	Stranded			
Remote Wiring Configuration Allowed	Yes			

Core & Coil (71A) HPS 200W - 400W

Max Ballast-Lamp Distance Remote V	Viring 2'				
Recommended Fuse Value	3 A				
Approval and Application					
Open Circuit Voltage Test (Volts)	170-210 V				
Approval Marks	ULR CSA certificate RoHS Compliant				
Temperature Marking	D				
UL Recognized	Yes				
Hipot Test (1 Minute)	2000 V				
Hipot Test (2 Seconds)	2500 V				
UL Insulation Class	H(180°C)				
UL Temperature Code	1029D				

Product Data	
Order product name	CORE & COIL HID HPS BAL 400W S51
	480V/120T KIT
EAN/UPC - Product	781087844311
Order code	913700577709
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700577709
Net Weight (Piece)	7.562 kg

Dimensional drawing



HPS BAL 400W S51 480V/120T KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 400W S51	4.3 in	2.8 in	4.8 in	4.4 in	4.3 in	3.9 in
480V/120T KIT						



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, March 22 - data subject to change