



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7503GY Switch Decorator 3WAY 15A 120/277V Gy *Eaton Wiring Devices*

Catalog Number	7503GY
Manufacturer	Eaton Wiring Devices
Description	Eaton Standard Grade Decorator Switch, Box, #14-12 Awg, 15A, Flush, 120/277V, Back/Push, Decorator, Maintained, Gray, Motor Control, Fan, Led, Incand, Elv, MLV, CFL, Florscnt, Halogen, Three-Way, Thermoplastic 627873
Weight per unit	0.2100 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	15A
dimensions	1.4400 IN X 0.9700 IN X 4.1900 IN
Material	Thermoplastic
Poles	Three-way
Voltage Rating	120/277 V

### Descriptions

Description	SWITCH DECORATOR 3WAY 15A 120/277V GY
extra long description	EWD 7503GY-BOX Switch Decorator 3Wa
Features	Eaton's Arrow Hart residential grade switches are engineered for smooth action and years of safe, dependable service - no matter what the application, type of load or use.
Long Description	Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Gray, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 627873
Product Type	Switch Decorator 3WAY 15A 120/277V Gy
Special Features	Box

### Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664627873
Manufacturers Part Number	7503GY-BOX
UPC	032664627873

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Standard grade decorator switch

### Packaging

Carton	1
Package	50
Weight Per each	0.21



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

standard

cULus Listed,NAFTA,RoHS Compliant