



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



75863 Stinger DS Led HP 120V Ac/12V DC *Streamlight, Inc.*

Catalog Number	75863
Manufacturer	Streamlight, Inc.
Description	Flashlight, Rechargeable, Compact, High Lumen, Industrial Safety Type; Black Color; Ce Approval; Machined Anodized Aluminum Body Material; Led Lamp Type; 1 Battery(S); Yes Battery Included; Stinger DS[R] Brand; Battery Type 3.6 Volt Nickel Metal Hydride
Weight per unit	N/A
Product Category	Flashlights, Lanterns, Warning

Features

Battery Included	Yes Yes/No
Lamp Type	LED
Number of Batteries	1 PH

Material, Color, and Finish

Body Material	Machined Anodized Aluminum
Color	BLACK

Descriptions

Additional Information	Battery Type 3.6 Volt Nickel Metal Hydride; Size 1.17 Inch Diameter x 9.65 Inch Length; Voltage Rating 120 Volt AC/12 Volt DC; Initial Intensity 200 to 800 Lumen; Light Output 12000 to 48000 Candela; Range of Light/Distance 438 Meter; Runtime 1.5 to 5 Hou
Commodity Description	FLASHLIGHTS, LANTERNS, WARNING LIGHTS
Description	STINGER DS LED HP 120V AC/12V DC
Long Description	FLASHLIGHT, RECHARGEABLE, COMPACT, HIGH LUMEN, INDUSTRIAL SAFETY TYPE; BLACK COLOR; CE APPROVAL; MACHINED ANODIZED ALUMINUM BODY MATERIAL; LED LAMP TYPE; 1 BATTERY(S); YES BATTERY INCLUDED; STINGER DS[R] BRAND; BATTERY TYPE 3.6 VOLT NICKEL METAL HYDRIDE
Product Type	Flashlight

Manufacturer Information

Brand	Streamlight, Inc.
GTIN	00080926758636
Manufacturers Part Number	75863
UPC	080926758636

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Rechargeable, Compact, High Lumen, Industrial Safety



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Approval	CE
----------	----