



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 774008 Toggle Switch, SPST, On-Off, Spade

*Ideal*

|                  |                                                                                                                                                                                                                                                                                                  |
|------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 774008                                                                                                                                                                                                                                                                                           |
| Manufacturer     | Ideal                                                                                                                                                                                                                                                                                            |
| Description      | Toggle Switch, 1 Pole, 10 A;20 A, 125/227 V Ac, SPST Contact Configuration, Solid Brass;Nickel-Plated (Bushing) Material, Spade Connection, Hole Mount, Nickel Plated (Bushing), 1.130 In (L) X 0.570 In (W) X 0.610 In (H), +32 °F Operating Temperature, +185 °F Operating Temperature, 0.1 LB |
| Weight per unit  | 0.1000 (lbs/each)                                                                                                                                                                                                                                                                                |
| Product Category | Gen Purpose Switches                                                                                                                                                                                                                                                                             |

### Features

|                  |                                                           |
|------------------|-----------------------------------------------------------|
| action           | SPST                                                      |
| actuator         | Toggle                                                    |
| amperage rating  | 10/20                                                     |
| connection       | Spade, 2 Terminals                                        |
| Contact Rating   | Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating |
| operating cycles | 100k                                                      |
| Poles            | 1                                                         |

### Dimensions and Weight

|      |                                                    |
|------|----------------------------------------------------|
| Size | 1.130 IN Length X 0.570 IN Width X 0.610 IN Height |
|------|----------------------------------------------------|

### Descriptions

|             |                                                                                                                                                                                                                                                                                                                      |
|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | TOGGLE SWITCH, SPST, ON-OFF, SPADE                                                                                                                                                                                                                                                                                   |
| Features    | Great for power tool and motor control switch applicationsRugged long-wearing solid brass/nickel-plated bushings1/2 in. diameter mounting holeDielectric Strength: 1500VMechanical Life: 100,000 cyclesOperating Temperature: 32°F to 185°F (0°C to 85°C)DC?Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Ideal          |
| GTIN  | 00783250573523 |
| UPC   | 783250573523   |

### Taxonomies, Classifications, and Categories

|                      |                  |
|----------------------|------------------|
| Category Description | TOGGLE SWITCHES  |
| Type                 | Standard, On-Off |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.1 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

|                             |                            |
|-----------------------------|----------------------------|
| Mounting .....              | 1/2 IN Hole Diameter ..... |
| Operating Temperature ..... | 32 To 185 .....            |
| standard .....              | CSA, RU Listed, RoHS ..... |