



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7623WBOX Switch Deco 3WAY 20A 120/277V Autogrd WH *Eaton Wiring Devices*

Catalog Number	7623WBOX
Manufacturer	Eaton Wiring Devices
Description	Eaton Commercial Grade Decorator Switch, Box, #14-10 Awg, 20A, Flush, 120/277V, Back/Push, Antimicrobial Paddle, Maintained, White, Motor Control, Fan, Led, Incand, Elv, MLV, CFL, Florscnt, Halogen, Three-Way, Thermoplastic 647390
Weight per unit	0.2400 (lbs/each)
Product Category	Gen Purpose Switches

Features

amperage rating	20A
dimensions	1.2900 IN X 1.1800 IN X 4.1900 IN
Material	Thermoplastic
Poles	Three-way
Voltage Rating	120/277 V

Descriptions

Description	SWITCH DECO 3WAY 20A 120/277V AUTOGRD WH
extra long description	EWD 7623W-BOX Switch Deco 3Way 20A
Features	Eaton's Arrow Hart commercial specification grade switches are designed to provide superior quality, reliability and performance in a variety of commercial environments.
Long Description	Eaton commercial grade decorator switch, Box, #14-10 AWG, 20A, Flush, 120/277V, Back/push, Antimicrobial paddle, Maintained, White, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Three-way, Thermoplastic 647390
Product Type	Switch Deco 3WAY 20A 120/277V Autogrd WH
Special Features	Box

Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664647390
Manufacturers Part Number	7623W-BOX
UPC	032664647390

Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Commercial grade decorator switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	50
Weight Per each	0.24

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL Listed,cULus Listed,RoHS Compliant