

Specifications



Photo is representative



Eaton 7737W-BOX

Eaton full LED nightlight, Dimmable, #14-12 AWG, 15A, Flush mount, 120V, Back and side wiring, White, Decorator, Thermoplastic

General specifications

PRODUCT NAME	Eaton full LED nightlight
CATALOG NUMBER	7737W-BOX
UPC	032664727764
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.226 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Full LED nightlight



Powering Business Worldwide

Product specifications

TYPE	Nightlight
AMPERAGE RATING	15A
VOLTAGE RATING	120 V
CONTACT MATERIAL	Brass
FEATURES	Dimmable
WIRING METHOD	Back and side
MOUNTING METHOD	Flush
PACKAGING TYPE	Retail Box
COLOR	White Gray
MATERIAL	Thermoplastic
STYLE	Decorator
WATTAGE	1W
ALLOWABLE WIRE SIZE	#14-12 AWG
TORQUE RATING	14 lbf-inch
COMBINATION TYPE	Night light
DESIGN TYPE	Full nightlight

Resources

BROCHURES	USB charging devices brochure
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 7737W-BOX Wallbox dimmable nightlight combination spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton 7737W-BOX

Eaton full LED nightlight, Dimmable, #14-12 AWG, 15A, Flush mount, 120V, Back and side wiring, White, Decorator, Thermoplastic

General specifications

PRODUCT NAME	Eaton full LED nightlight
CATALOG NUMBER	7737W-BOX
UPC	032664727764
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.226 lb
CERTIFICATIONS	cULus Listed NOM
PRODUCT TYPE	Full LED nightlight



Powering Business Worldwide

Product specifications

TYPE	Nightlight
AMPERAGE RATING	15A
VOLTAGE RATING	120 V
CONTACT MATERIAL	Brass
FEATURES	Dimmable
WIRING METHOD	Back and side
MOUNTING METHOD	Flush
PACKAGING TYPE	Retail Box
COLOR	White Gray
MATERIAL	Thermoplastic
STYLE	Decorator
WATTAGE	1W
ALLOWABLE WIRE SIZE	#14-12 AWG
TORQUE RATING	14 lbf-inch
COMBINATION TYPE	Night light
DESIGN TYPE	Full nightlight

Resources

BROCHURES	USB charging devices brochure
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 7737W-BOX Wallbox dimmable nightlight combination spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

