



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2020 Farmerville Highway
71270-0000, LA Ruston
Phone: 318-251-9393
Fax: 318-255-1402



78130TQ 20AMP DPST On/Off Bat TGL SWITCH

Nsi Industries

| | |
|------------------|---|
| Catalog Number | 78130TQ |
| Manufacturer | Nsi Industries |
| Description | On Off - DPST - Nickel .250 Quikconnect Bat Toggle Switch |
| Weight per unit | 0.0800 (lbs/each) |
| Product Category | Selector Switch Complete Assem |

Features

| | |
|-----------------------|-------------------------------------|
| action | Toggle Switch |
| amperage rating | 10;20 |
| Contact Configuration | DPST |
| Contact Rating | 20 Amp (125 VAC) - 10 Amp (250 VAC) |
| Poles | 2 |
| Switch Type | NSI |
| Voltage Rating | 125-250 VAC |
| Warranty | 1 YEAR |

Dimensions and Weight

| | |
|--------|------|
| Height | .778 |
| Width | .750 |

Descriptions

| | |
|------------------------|---|
| Description | 20AMP DPST ON/OFF BAT TGL SWITCH |
| extra long description | NSI 78130TQ Toggle Switch DPST 20 |
| Features | ON OFF - DPST - Nickel .250 QuikConnect Bat Toggle Switch |
| Long Description | ON OFF - DPST - Nickel .250 QuikConnect Bat Toggle Switch |
| Product Type | Toggle Switch DPST 20 Amps On-Off Circuit Bat BR/Ni Quick C |
| Special Features | DPST - On-Off - Quick Connect Terminals |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381781307 |
| Manufacturers Part Number | 78130TQ |
| UPC | 662381781307 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------|
| Category Description | TOGGLE SWITCHES |
| Type | TOGGLE SWITCH |

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Package | 1 |
| Weight Per each | 0.08 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2020 Farmerville Highway
71270-0000, LA Ruston
Phone: 318-251-9393
Fax: 318-255-1402

Uses, Certifications, and Standards

Application Motor-Equipment Control
Mounting Snap Mount