



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 806 3/4" Flex 90 Degree Malleable Iron Squeeze Conn *Bridgeport Fittings*

Catalog Number	806
Manufacturer	Bridgeport Fittings
Description	
Weight per unit	0.2700 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

angle	90 DEG
Connector Type	FMC
Material	MALLEABLE IRON
media	Yes
Trade Size	3/4 in

### Material, Color, and Finish

Finish	Zinc electro-plate
--------	--------------------

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Description	3/4" FLEX 90 DEGREE MALLEABLE IRON SQUEEZE CONN
Product Type	3/4 Angle Conn.

### Manufacturer Information

Brand	Bridgeport
GTIN	00781747008060
UPC	781747008060

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

### Packaging


Carton	10
Package	50
Weight Per each	0.27

### Uses, Certifications, and Standards

Application	90 Degrees fitting with cover for connecting flexible metal conduit to box or enclosure.
standard	UL,CSA

## 90° - Large Size- Malleable

### Images



[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 1-13/16

Dimension B in Inches: 1/2

Dimension C in Inches: 1-1/2

Dimension D in Inches: 9/16

Dimension E in Inches: .750

Dimension F in Inches: 1-1/2

### Application

90 Degrees fitting with cover for connecting flexible metal conduit to box or enclosure.

### Product Information

Material: Malleable Iron

Finish: Zinc electro-plate

### Certifications & Codes:

CSA File Number: LR39354

Federal Specification Number: A-A-50552

NEMA Standard: FB-1

UL File Number: E9391

UL Standard: UL-514B

UNSPSC: 39121419

**Catalog ID:** 806

**UPC Number:** 781747008060

**Description:** Connector, 90 Degrees, Malleable Iron, Flex Size 3/4 Inch

**Application:** 90 Degrees fitting with cover for connecting flexible metal conduit to box or enclosure.

**Trade Size:** 3/4"

**Std Pkg Qty:** 50

**Unit Qty:** 10