



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## 839301 Vinyl Insul Butt Splice, Yellow 12-10 Awg, 25/Box

*Ideal*

Catalog Number	839301
Manufacturer	Ideal
Description	Ideal, Splice Terminal, Vinyl Butt, Size: 12 to 10 Awg, Material: Brass, Finish: Tin-Plated, Voltage Rating: 600 V Max, Temperature Rating: 75 Deg C
Weight per unit	0.2000 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Material	Brass
Voltage Rating	600 V Max

### Material, Color, and Finish

Finish	Tin-Plated
--------	------------

### Dimensions and Weight

Size	12 To 10
------	----------

### Descriptions

Description	VINYL INSUL BUTT SPLICE, YELLOW 12-10 AWG, 25/BOX
extra long description	IDEAL 83-9301 TRM BUT SPL VINL 12-1
Features	Butted seam-construction prevents splitting under maximum pressureInternal barrel serrations grip wires tightly to resist pull-out and reduce electrical resistanceTin-plated brass construction for corrosion resistanceShouldered barrel insulation quickly positions terminal for proper crimpingExpanded insulation entry accommodates a wide variety of insulation diameters and provides additional insulation supportThe complete line of IDEAL crimp terminals, disconnects, and splices offer the right product for an
Long Description	IDEAL, Splice Terminal, Vinyl Butt, Size: 12 To 10 AWG, Material: Brass, Finish: Tin-plated, Voltage Rating: 600 V Max, Temperature Rating: 75 DEG C
Product Type	TRM But SPL Vinl 12-10AWG-25PK
Special Features	Features: Tin-Plated Brass Construction For Corrosion Resistance; Brazed Or Butted Seams Prevent Splitting; Funnel Entry Insulators; Beveled Barrel Openings Provide Easy Wire Entry; Clearly Marked Wire And Stud Ranges; Color-Coded Insulation



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Manufacturer Information

Brand	Ideal
GTIN	00783250490462
Manufacturers Part Number	83-9301
UPC	783250490462

## Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	Vinyl Butt

## Availability

minimum qty	25
-------------	----

## Packaging

Carton	25
Weight Per each	0.2

## Uses, Certifications, and Standards

standard	CUL Listed, RoHS
Temperature Rating	75