



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



840B 6" Plastic Bushing

Topaz - Southwire LLC

Catalog Number	840B
Manufacturer	Topaz - Southwire LLC
Description	Rigid Conduit Insulating Bushing, Threaded Female Type; Thermoplastic Material; 1 Inch; Imc/Rigid Conduit Used On; UL, Csa Approval; 7.5 Inch Diameter; 105 Deg C Temperature Rating; 10 Per Case Standard Package; 6 Inch Trade Size
Weight per unit	0.1600 (lbs/each)
Product Category	Plastic

Features

Material	Thermoplastic
Throat Type	PLASTIC INSULATED

Dimensions and Weight

Diameter	7.5 Inch
Height	1 INCH

Descriptions

Commodity Description	Rigid Conduit Fittings - Plastic
Description	6" PLASTIC BUSHING
extra long description	FEMALE THREADED TYPE; THERMOPLASTIC MATERIAL; 1 INCH; IMC/RIGID CONDUIT USED ON; UL (CANADA AND US) APPROVAL; 7.5 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 10 PER CASE STANDARD PACKAGE; 6 INCH TRADE SIZE; PLASTIC INSULATED THROAT TYPE; APPLICATION INDOOR, OUTDOOR
Long Description	RIGID CONDUIT INSULATING BUSHING, THREADED FEMALE TYPE; THERMOPLASTIC MATERIAL; 1 INCH; IMC/RIGID CONDUIT USED ON; UL, CSA APPROVAL; 7.5 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 10 PER CASE STANDARD PACKAGE; 6 INCH TRADE SIZE
Product Type	Rigid Conduit Insulating Bushing

Manufacturer Information

Brand	Southwire Rough Electrical Com
GTIN	00751338185609
Manufacturers Part Number	840B
UPC	751338185609

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	THREADED FEMALE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size	6 INCH
------------	--------

Packaging

Carton	1
Package	10
Standard Package	10 PER CASE
Weight Per each	0.16

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	105 DEG C
Used On	IMC/RIGID CONDUIT