



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291



831TZ 1/2" Plastic Bushing

Topaz - Southwire LLC

Catalog Number	831TZ
Manufacturer	Topaz - Southwire LLC
Description	Rigid Conduit Insulating Bushing, Threaded Female Type; Thermoplastic Material; 0.43 Inch; Imc/Rigid Conduit Used On; Ul, Csa Approval; 1.06 Inch Diameter; 105 Deg C Temperature Rating; 1000 Per Case Standard Package; 1/2 Inch Trade Size
Weight per unit	N/A
Product Category	Plastic

Features

Material	Thermoplastic
Throat Type	PLASTIC INSULATED

Dimensions and Weight

Diameter	1.06 INCH
Height	0.43 Inch

Descriptions

Commodity Description	Rigid Conduit Fittings - Plastic
Description	1/2" PLASTIC BUSHING
extra long description	FEMALE THREADED TYPE; THERMOPLASTIC MATERIAL; 0.43 INCH; IMC/RIGID CONDUIT USED ON; UL (CANADA AND US) APPROVAL; 1.06 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 1000 PER CASE STANDARD PACKAGE; 1/2 INCH TRADE SIZE; PLASTIC INSULATED THROAT TYPE; APPLICATION INDOOR, OUTDOOR
Long Description	RIGID CONDUIT INSULATING BUSHING, THREADED FEMALE TYPE; THERMOPLASTIC MATERIAL; 0.43 INCH; IMC/RIGID CONDUIT USED ON; UL, CSA APPROVAL; 1.06 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 1000 PER CASE STANDARD PACKAGE; 1/2 INCH TRADE SIZE
Product Type	Rigid Conduit Insulating Bushing

Manufacturer Information

Brand	TOPAZ ELECTRIC CORP
GTIN	00751338184503
Manufacturers Part Number	831TZ
UPC	751338184503

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	THREADED FEMALE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street
66046-0000, KS Lawrence
Phone: 785-330-9441
Fax: 785-371-0291

Trade Size

Trade Size 1/2 INCH

Packaging

Carton 1
Standard Package 1000 PER CASE
Weight Per each 0

Uses, Certifications, and Standards

Approval UL, CSA
Temperature Rating 105 DEG C
Used On IMC/RIGID CONDUIT