



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



839 3-1/2" Plastic Bushing

Topaz - Southwire LLC

Catalog Number	839
Manufacturer	Topaz - Southwire LLC
Description	Rigid Conduit Insulating Bushing, Threaded Female Type; Thermoplastic Material; 0.77 Inch; Imc/Rigid Conduit Used On; Ul, Csa Approval; 4.37 Inch Diameter; 105 Deg C Temperature Rating; 25 Per Case Standard Package; 3-1/2 Inch Trade Size
Weight per unit	N/A
Product Category	Plastic

Features

Material	Thermoplastic
Throat Type	PLASTIC INSULATED

Dimensions and Weight

Diameter	4.37 INCH
Height	0.77 INCH

Descriptions

Commodity Description	Rigid Conduit Fittings - Plastic
Description	3-1/2" PLASTIC BUSHING
extra long description	FEMALE THREADED TYPE; THERMOPLASTIC MATERIAL; 0.77 INCH; IMC/RIGID CONDUIT USED ON; UL (CANADA AND US) APPROVAL; 4.37 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 25 PER CASE STANDARD PACKAGE; 3-1/2 INCH TRADE SIZE; PLASTIC INSULATED THROAT TYPE; APPLICATION INDOOR, OUTDOOR
Long Description	RIGID CONDUIT INSULATING BUSHING, THREADED FEMALE TYPE; THERMOPLASTIC MATERIAL; 0.77 INCH; IMC/RIGID CONDUIT USED ON; UL, CSA APPROVAL; 4.37 INCH DIAMETER; 105 DEG C TEMPERATURE RATING; 25 PER CASE STANDARD PACKAGE; 3-1/2 INCH TRADE SIZE
Product Type	Rigid Conduit Insulating Bushing

Manufacturer Information

Brand	SOUTHWIRE ROUGH ELECTRICAL COMPONENTS
GTIN	00751338185302
UPC	751338185302

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	THREADED FEMALE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size	3-1/2 INCH
------------	------------

Packaging

Carton	1
Package	25
Standard Package	25 PER CASE
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL, CSA
Temperature Rating	105 DEG C
Used On	IMC/RIGID CONDUIT