

Night Com® Tactical Light



- Material/Lens** Corrosion resistant and O-ring sealed for all extreme weather operation. This light is manufactured using aircraft grade aluminum. The Night Com is coated with Mil Spec Type II anodize for superior wear and abrasion resistance. Unbreakable polycarbonate lens
- Dims/Weight** Length: 5.43 in (13.79 cm) Diameter: Major Diameter: 1.33 in. (3.38 cm) Body Diameter: 0.98 in. (2.49 cm)
5.44 oz (152 grams)
- Light Source** C4® LED: 4,500 candela peak beam intensity; 105 lumens; runs 3.5 hours
Ultra-bright red LEDs: 2.5 lumens; runs 28 hours
Indicator Type LED: Preserves complete dark adaptation per MIL-1472D (<0.05 lumens)
- Switch** Push-button tail switch: On/Off
Secondary mode selector switch: Sequence - Two ultra-bright red LEDs / Indicator-type LED / C4 LED / Safe
- Battery** Two CR123A lithium batteries (included)
- Features**
- Micro Faceted Reflector for Smooth Focus, O Ring sealed, weather resistant, heavy duty drop-tested construction
 - Mode Select Switch, On/Off/Safe tailcap switch
 - High strength wrist lanyard
- Approvals** Most models meet applicable European Community Directives
- Warranty** Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
Night Com with lithium batteries. Blister Packaged.	080926-51056-2	51056
Lithium batteries (2) Pack	080926-85175-7	85175
Lithium batteries (12) Pack	080926-85177-1	85177
Lithium batteries (400) Pack	080926-85179-5	85179
Lithium batteries (6) Pack	080926-85180-1	85180

Made in China



STREAMLIGHT



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight, Inc. Night Com 7/13

Night Com® Tactical Light



Material/Lens Corrosion resistant and O-ring sealed for all extreme weather operation. This light is manufactured using aircraft grade aluminum. The Night Com is coated with Mil Spec Type II anodize for superior wear and abrasion resistance. Unbreakable polycarbonate lens

Dims/Weight Length: 5.43 in (13.79 cm) Diameter: Major Diameter: 1.33 in. (3.38 cm) Body Diameter: 0.98 in. (2.49 cm)
5.44 oz (152 grams)

Light Source C4® LED: 4,500 candela peak beam intensity; 105 lumens; runs 3.5 hours
Ultra-bright red LEDs: 2.5 lumens; runs 28 hours
Indicator Type LED: Preserves complete dark adaptation per MIL-1472D (<0.05 lumens)

Switch Push-button tail switch: On/Off
Secondary mode selector switch: Sequence - Two ultra-bright red LEDs / Indicator-type LED / C4 LED / Safe

Battery Two CR123A lithium batteries (included)

Features

- Micro Faceted Reflector for Smooth Focus, O Ring sealed, weather resistant, heavy duty drop-tested construction
- Mode Select Switch, On/Off/Safe tailcap switch
- High strength wrist lanyard

Approvals Most models meet applicable European Community Directives

Warranty Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction.

Item	UPC	Part #
Night Com with lithium batteries. Blister Packaged.	080926-51056-2	51056
Lithium batteries (2) Pack	080926-85175-7	85175
Lithium batteries (12) Pack	080926-85177-1	85177
Lithium batteries (400) Pack	080926-85179-5	85179
Lithium batteries (6) Pack	080926-85180-1	85180



Made in China



30 Eagleville Road • Eagleville, PA 19403 • 610-631-0600/800-523-7488 Phone • 610-631-0712/800-220-7007 Fax
www.streamlight.com ©Streamlight, Inc. Night Com 7/13