



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298



8644XSCHC Encl 8X6X4 N4X SS CH CLMP CVR *Cooper B-Line/Cable Tray*

Catalog Number	8644XSCHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 8" Height, 4" Length, 6" Width, Nema 4X, Hinged Cover, 4XSCHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	4.7 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	4.0000 IN X 6.0000 IN X 8.0000 IN
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	6.00 In Width X 4.00 In Depth X 8.00 In Height
------	--

Descriptions

Description	ENCL 8X6X4 N4X SS CH CLMP CVR
extra long description	B-LINE 864-4XSCHC TYPE 4X SSL JIC C
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 8" height, 4" length, 6" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL Jic Continuous Hinge CVR Enc, 8X6X4
Special Features	Cont. piano hinge,panel mount prov.,s.s.doorclamps

Manufacturer Information

Brand	Eaton
GTIN	00782051702941
Manufacturers Part Number	864-4XSCHC
UPC	782051702941

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298

Packaging

Carton	1
Weight Per each	4.737

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Mfg. Process Electrification and Control Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Ind Facilities & Factories - Facility: Lighting and Lighting Controls Ind Facilities & Factories - Facility: Automation and Monitoring Ind Facilities & Factories - Industrial Facilities/Factories - Other Ind Facilities & Factories - Facility: Power Distribution and Control Ind Facilities & Factories - Facility: Critical Power Ind Facilities & Factories - Facility
Mounting	EXTERNAL FEET, WALL
nema rating	4X
standard	NEMA,CSA C22.2.,UL 50