



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Andrew Dr  
30281-0000, GA Stockbridge  
Phone: 470-440-4222  
Fax: 678-369-9160



## 8822 3", 22-1/2D Emt Elb *Topaz - Southwire LLC*

Catalog Number	8822
Manufacturer	Topaz - Southwire LLC
Description	Emt Conduit Elbow, Steel Material; Galvanized Finish; UI 797, Csa Approval; Ansi C80.3, WW-C-563 Applicable Standard; 1 Per Case Standard Package; 3 Inch Trade Size; Plain End Type; 22 Degree Bend Angle; 13 Inch Bend Radius
Weight per unit	7.2 (lbs/each)
Product Category	Emt to Emt Pulling Elbows

### Features

Applicable Standard	ANSI C80.3, WW-C-563
Bend Angle	22 Degree
Bend Radius	13 INCH
End Type	Plain
Material	Steel

### Material, Color, and Finish

Finish	Galvanized
--------	------------

### Descriptions

Commodity Description	Emt To Emt Pulling Elbows
Description	3",22-1/2D EMT ELB
extra long description	STEEL MATERIAL; GALVANIZED FINISH; UL 797, CSA APPROVAL; ANSI C80.3, WW-C-563 APPLICABLE STANDARD; 1 PER CASE STANDARD PACKAGE; 3 INCH TRADE SIZE; PLAIN END TYPE; 22 DEGREE BEND ANGLE; 13 INCH BEND RADIUS
Long Description	EMT CONDUIT ELBOW, STEEL MATERIAL; GALVANIZED FINISH; UL 797, CSA APPROVAL; ANSI C80.3, WW-C-563 APPLICABLE STANDARD; 1 PER CASE STANDARD PACKAGE; 3 INCH TRADE SIZE; PLAIN END TYPE; 22 DEGREE BEND ANGLE; 13 INCH BEND RADIUS
Product Type	Emt Conduit Elbow

### Manufacturer Information

Brand	TOPAZ ELECTRIC CORP
Manufacturers Part Number	8822

### Taxonomies, Classifications, and Categories

Category Description	EMT ELBOWS
----------------------	------------

### Trade Size

Trade Size	3 INCH
------------	--------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Andrew Dr  
30281-0000, GA Stockbridge  
Phone: 470-440-4222  
Fax: 678-369-9160

## Packaging

Carton	1
Standard Package	1 PER CASE
Weight Per each	7.2

## Uses, Certifications, and Standards

Approval	UL 797, CSA
----------	-------------