



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8922 3-1/2" 22-1/2D Elbow Emt

Topaz - Southwire LLC

Catalog Number	8922
Manufacturer	Topaz - Southwire LLC
Description	Emt Conduit Elbow, Steel Material; Galvanized Finish; UL 797, Csa Approval; Ansi C80.3, WW-C-563 Applicable Standard; 1 Per Case Standard Package; 3-1/2 Inch Trade Size; Plain End Type; 22 Degree Bend Angle; 15 Inch Bend Radius
Weight per unit	N/A
Product Category	Emt to Emt Pulling Elbows

Features

Applicable Standard	ANSI C80.3, WW-C-563
Bend Angle	22 Degree
Bend Radius	15 INCH
End Type	Plain
Material	Steel

Material, Color, and Finish

Finish	Galvanized
--------	------------

Descriptions

Commodity Description	Emt To Emt Pulling Elbows
Description	3-1/2" 22-1/2D ELBOW EMT
extra long description	STEEL MATERIAL; GALVANIZED FINISH; UL 797, CSA APPROVAL; ANSI C80.3, WW-C-563 APPLICABLE STANDARD; 1 PER CASE STANDARD PACKAGE; 3-1/2 INCH TRADE SIZE; PLAIN END TYPE; 22 DEGREE BEND ANGLE; 15 INCH BEND RADIUS
Long Description	EMT CONDUIT ELBOW, STEEL MATERIAL; GALVANIZED FINISH; UL 797, CSA APPROVAL; ANSI C80.3, WW-C-563 APPLICABLE STANDARD; 1 PER CASE STANDARD PACKAGE; 3-1/2 INCH TRADE SIZE; PLAIN END TYPE; 22 DEGREE BEND ANGLE; 15 INCH BEND RADIUS
Product Type	Emt Conduit Elbow

Manufacturer Information

Brand	SOUTHWIRE ROUGH ELECTRICAL COMPONENTS
Manufacturers Part Number	8922

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Trade Size

Trade Size	3-1/2 INCH
------------	------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	35
Standard Package	1 PER CASE
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL 797, CSA
----------	-------------