





Catalog Number: 884-SC1-NK
Item Description: N1 SCREW COVER ENCL NK
UPC Code: 784572109407

Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.



| CATALOG# | LABEL# |
|----------------|---------|
| 884-SC1-() | 1002135 |
| RC-884-SC1-() | 1125021 |
| SPSC-884() | 1132714 |



| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|---------------------|
| 1 | 4 | 1001290 | SCREW, 10-32 X 5/16 |
| 2 | 1 | (SEE CHART) | U/L LISTING LABEL |
| 3 | 1 | 1002135 | LABEL (UL) |
| 4 | 1 | 1002475 | 1002170 |
| 5 | 2 | 1010875 | BOTTOM |
| 6 | 1 | 1001367 | BACK |
| 7 | 1 | 1157537 | PLATE |

| CRS CHART | | | |
|-------------|------------|--------|--------------------|
| SUFFIX | WELDMENT # | K.O.'s | FINISH |
| NP | 1153805 | YES | NONE |
| NP-NK | 1153806 | NO | |
| NONE | 1153809 | YES | MILBANK LIGHT GRAY |
| NK | 1000697 | NO | |
| GALV. CHART | | | |
| NP | 1011163 | YES | NONE |
| NP-NK | 1153807 | NO | |
| NONE | 1109524 | YES | MILBANK LIGHT GRAY |
| NK | 1153808 | NO | |



| CRS CHART | | |
|-------------|---------|--------------------|
| SUFFIX | PLATE # | FINISH |
| NONE | 1103848 | MILBANK LIGHT GRAY |
| NP | 1003327 | NONE |
| GALV. CHART | | |
| NONE | 1003704 | MILBANK LIGHT GRAY |
| NP | 1003328 | NONE |



NOTES:

- 1.) BAG ASSY TO BE SHIPPED INSIDE OF EACH ENCLOSURE.
- 2.) WHEN SOLD WITH "R" PREFIX, APPLY STANDARD CARTON LABEL SHOWING QUANTITY OF 1 TO THE WRAPPING OF EACH UNIT. APPLY STANDARD CARTON LABEL TO CARTON SHOWING QUANTITY OF 4.

| REV. | DATE | DESCRIPTION | BY |
|------|---------|---|------|
| F | 2/21/14 | REMOVED KO'S FROM BACK eECR2722 | AJS |
| E4 | 12/5/11 | UPDATE RETAIL NOTE (ECO #21645) | D.F. |
| E5 | 5/16/12 | NOTE 2: "THE WRAPPING" WAS "SHRINK WRAP" (ECO #22340) | D.F. |

| | | | | | |
|--|--|--|--|---|--|
| Material: | | 16 GA. GALV. STEEL | |  | |
| Shear/ Die#: | | | | | |
| Finish: | | MILBANK LIGHT GRAY | | General Offices: Kansas City, MO | |
| Part Wt.: | | | | Title: | 884 SCREW COVER TYPE 1 ENCLOSURE |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2° | | Third Angle  | | Catalog No.: | |
| Scale: | | NTS | | Customer: | MILBANK STANDARD |
| Drawn By: | | DY | | Drawing No.: | 1002641 |
| Checked By: | | | | Date: | 04/26/01 |
| Approved By: | | | | Sheet | 1 of 1 |





Catalog Number: 884-SC1-NK
Item Description: N1 SCREW COVER ENCL NK
UPC Code: 784572109407

Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.



| CATALOG# | LABEL# |
|----------------|---------|
| 884-SC1-() | 1002135 |
| RC-884-SC1-() | 1125021 |
| SPSC-884() | 1132714 |



| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|---------------------|
| 1 | 4 | 1001290 | SCREW, 10-32 X 5/16 |
| 2 | 1 | (SEE CHART) | U/L LISTING LABEL |
| 3 | 1 | 1002135 | LABEL (UL) |
| 4 | 1 | 1002475 | 1002170 |
| 5 | 2 | 1010875 | BOTTOM |
| 6 | 1 | 1001367 | BACK |
| 7 | 1 | 1157537 | PLATE |

| CRS CHART | | | |
|-------------|------------|--------|--------------------|
| SUFFIX | WELDMENT # | K.O.'s | FINISH |
| NP | 1153805 | YES | NONE |
| NP-NK | 1153806 | NO | |
| NONE | 1153809 | YES | MILBANK LIGHT GRAY |
| NK | 1000697 | NO | |
| GALV. CHART | | | |
| NP | 1011163 | YES | NONE |
| NP-NK | 1153807 | NO | |
| NONE | 1109524 | YES | MILBANK LIGHT GRAY |
| NK | 1153808 | NO | |



| CRS CHART | | |
|-------------|---------|--------------------|
| SUFFIX | PLATE # | FINISH |
| NONE | 1103848 | MILBANK LIGHT GRAY |
| NP | 1003327 | NONE |
| GALV. CHART | | |
| NONE | 1003704 | MILBANK LIGHT GRAY |
| NP | 1003328 | NONE |



NOTES:

- 1.) BAG ASSY TO BE SHIPPED INSIDE OF EACH ENCLOSURE.
- 2.) WHEN SOLD WITH "R" PREFIX, APPLY STANDARD CARTON LABEL SHOWING QUANTITY OF 1 TO THE WRAPPING OF EACH UNIT. APPLY STANDARD CARTON LABEL TO CARTON SHOWING QUANTITY OF 4.

| REV. | DATE | DESCRIPTION | BY |
|------|---------|---|------|
| F | 2/21/14 | REMOVED KO'S FROM BACK eECR2722 | AJS |
| E4 | 12/5/11 | UPDATE RETAIL NOTE (ECO #21645) | D.F. |
| E5 | 5/16/12 | NOTE 2: "THE WRAPPING" WAS "SHRINK WRAP" (ECO #22340) | D.F. |

| | | | | | | | |
|--|--|--|--|---|--|--|--|
| Material: | | 16 GA. GALV. STEEL | |  | | | |
| Shear/ Die#: | | | | | | | |
| Finish: | | MILBANK LIGHT GRAY | | General Offices: Kansas City, MO | | | |
| Part Wt.: | | | | Title: | | 884 SCREW COVER TYPE 1 ENCLOSURE | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2° | | Third Angle  | | Catalog No.: | | | |
| Y S | | | | Customer: | | MILBANK STANDARD | |
| F. | | Scale: NTS | | Checked By: | | | |
| Drawn By: | | DY | | Approved By: | | | |
| | | | | Date: | | 04/26/01 | |
| | | | | Sheet | | 1 of 1 | |
| | | | | Drawing No.: | | 1002641 | |