

Compression Connectors



RTQ™ Reg/Tri/Quad & Plenum F-Connectors

- Fits 60% regular, tri-shield and quad shield cables
- Nickel-plated, brass-construction for superior corrosion resistance
- Designed for use by satellite and cable TV companies
- Weatherproof for indoor and outdoor use
- Use 30-603, 30-793 or 30-633 Compression Tools

RG-11 F-Connectors

- Fits 60% regular RG-11 cable
- Nickel-plated, brass-construction for superior corrosion resistance
- Designed for use by satellite and cable TV companies
- Weatherproof for indoor and outdoor use
- Use 30-603 or 30-793 Compression Tools
- Use 45-111, 1/4" x 1/4" RG-11 Coax Stripper




BNC Connectors

- Nickel-plated, brass-construction for superior corrosion resistance
- Moisture-inhibiting design
- Use 30-793 Compression Tool
- 75 Ohm nominal impedance
- Gold-plated pin contact area
- Available in plenum versions

OmniCONN™ F-Connectors

- Non corrosive nickel plated brass body and polycarbonate bushing
- Delrin/Nylon adapter sleeve and o-ring provide double protection for a watertight seal
- Free spinning hex nut for ease of installation onto all 7/16 ports
- 75 ohm nominal impedance
- Two-piece pre-assembled connectors



RCA Connectors

- Constructed of nickel plated brass and gold plated head
- 75 ohm nominal impedance
- Bandwidth up to 3 GHz
- Compatible with 30-603 and 30-793 Compression Tools

Compression Connectors

	Connector Type	Cable Type	Qty.	Cat. No.
	F	RG-6 Reg/Tri/Quad	Card of 4	92-654
			Card of 10	92-651
			Jar of 50	92-650
			Jar of 100	92-656
			Box of 1,000 (20 bags of 50 ea.)	92-759
			Box of 1,000 bulk	92-659
	F	RG-6 Plenum	Jar of 50	92-660
			Box of 1,000	92-669
	F	RG-59 Reg/Tri/Quad	Jar of 50	92-610
			Box of 1,000	92-619
	F	RG-11	Card of 10	89-211
			Box of 500	89-1211
	F	RG-6	Jar of 50	89-044
			Box of 1,500	89-1544
	F	Quad	Jar of 50	89-045
			Box of 1,500	89-1545
	BNC	RG-6	Card of 4	92-705
			Card of 15	89-048
			Jar of 35	89-5048
			Box of 1,000 (10 bags, 100 ea.)	89-1048
	BNC	RG-6 Plenum	Card of 15	89-050
			Jar of 35	89-5050
			Box of 1,000 (10 bags, 100 ea.)	89-1050
	BNC	RG-59	Card of 4	92-704
			Card of 15	89-047
			Jar of 35	89-5047
			Box of 1,000 (10 bags, 100 ea.)	89-1047
	BNC	RG-59 Plenum	Card of 15	89-049
			Jar of 35	89-5049
			Box of 1,000 (10 bags, 100 ea.)	89-1049
	RCA*	RG-6	Card of 4	92-582
			Card of 10	89-582
			Jar of 35	89-580
	RCA*	RG-59	Card of 4	92-572
			Card of 10	89-572
			Jar of 35	89-570
	RCA	Mini (21 - 23 AWG)	Card of 10	89-014SMRCA

*RCA Connectors include an assortment of color ID bands.

Compression Port Seals - 1/2 in.

- Used with compression F-connectors to weatherproof connector by placing onto the female port. Made from EPDM for superior sealing.



Description	Qty.	Cat. No.
Long Sleeve Compression F-Connector Port Seals, 1/2 in.	Bag of 100	89-127