

Products

- › [Index](#)
- › [Featured Products](#)
- › [Cross Reference](#)
- › [UPC Search](#)

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

911-3 -- 4" Square Box, 2-1/8" Deep, Painted Red, 1/2" & 3/4" Side Knockouts, Welded



Product Specifications

Box Type	RACO Steel Boxes & Covers
Box Family	4" Square Boxes, Covers, Extension Rings
Box Category	4" Square Boxes - For Conduit
Category	Red Alarm Support Boxes
Box Depth	2-1/8"
Side Knockout(s)	8, 1/2" & 4, TKO
Bottom Knockout(s)	3, 1/2" & 2, TKO
Bracket Setback	Flush
Drawn or Welded	Welded
Cubic Inch Capacity	30.3
Color	Red, polyester powder
UPC Number	050169091135
Product UPC-A Labeled	No
Minimum Pack Qty.	25
Inner Leaf 2 of 5 Bar Code	50050169091130
Unit Carton Quantity	25
Ship Carton Length (In.)	18.5
Ship Carton Width (In.)	7.125
Ship Carton Height (In.)	8.38
Weight (Per/C)	90.2
Pallet Quantity	1,750
Fire Resistance	Acceptable for use in 2-hour rated walls
Dimension A	2-1/8"

Applications


- Accommodates local codes for easy identification of products relative to life safety systems
- For use in industrial, commercial, or residential applications

Product Features

- Durable, UL listed bright red polyester powder finish
- Features RACO's patented TKO 1/2" & 3/4" eccentric knockouts

Compliances

UL listed



Products

- › [Index](#)
- › [Featured Products](#)
- › [Cross Reference](#)
- › [UPC Search](#)

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

911-3 -- 4" Square Box, 2-1/8" Deep, Painted Red, 1/2" & 3/4" Side Knockouts, Welded



Product Specifications

Box Type	RACO Steel Boxes & Covers
Box Family	4" Square Boxes, Covers, Extension Rings
Box Category	4" Square Boxes - For Conduit
Category	Red Alarm Support Boxes
Box Depth	2-1/8"
Side Knockout(s)	8, 1/2" & 4, TKO
Bottom Knockout(s)	3, 1/2" & 2, TKO
Bracket Setback	Flush
Drawn or Welded	Welded
Cubic Inch Capacity	30.3
Color	Red, polyester powder
UPC Number	050169091135
Product UPC-A Labeled	No
Minimum Pack Qty.	25
Inner Leaf 2 of 5 Bar Code	50050169091130
Unit Carton Quantity	25
Ship Carton Length (In.)	18.5
Ship Carton Width (In.)	7.125
Ship Carton Height (In.)	8.38
Weight (Per/C)	90.2
Pallet Quantity	1,750
Fire Resistance	Acceptable for use in 2-hour rated walls
Dimension A	2-1/8"

Applications

- Accommodates local codes for easy identification of products relative to life safety systems
- For use in industrial, commercial, or residential applications

Product Features

- Durable, UL listed bright red polyester powder finish
- Features RACO's patented TKO 1/2" & 3/4" eccentric knockouts

Compliances

UL listed

