



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116
85027-0000, AZ Phoenix
Phone: 480-681-0668
Fax: 480-681-0669



944A 6V HD Lantern Battery

Rayovac Corporation

Catalog Number	944A
Manufacturer	Rayovac Corporation
Description	Lantern Battery, Lantern Heavy Duty Type; 2.685 Inch; 4.528 Inch; 6 Volt Voltage Rating; Spring Terminal Type; Rayovac Brand; Shell Material Plastic; Temperature Rating -30 to 55 Deg C; Application Industrial; Applicable Standard Ansi/Neda, Epa
Weight per unit	N/A
Product Category	Batteries & Chargers

Features

Terminal Type	Spring
Voltage Rating	6 Volt

Dimensions and Weight

Height	4.528 Inch
Width	2.685 Inch

Descriptions

Additional Information	Shell Material Plastic; Temperature Rating -30 to 55 Deg C; Application Industrial; Applicable Standard ANSI/NEDA, EPA
Commodity Description	BATTERIES & CHARGERS
Description	6V HD LANTERN BATTERY
extra long description	LANTERN HEAVY DUTY TYPE; 2.63 INCH; 2.63 INCH; 4.5 INCH; 6 VOLT VOLTAGE RATING; SPRING TERMINAL TYPE; ULTRA PRO[™] BRAND; TEMPERATURE RATING -20 TO 130 DEG F; MATERIAL CARBON ZINC (CELL), PLASTIC (SHELL); APPLICATION INDUSTRIAL; APPLICABLE STANDARD ANSI/NEDA, IEC, EPA
Long Description	LANTERN BATTERY, LANTERN HEAVY DUTY TYPE; 2.685 INCH; 4.528 INCH; 6 VOLT VOLTAGE RATING; SPRING TERMINAL TYPE; RAYOVAC BRAND; SHELL MATERIAL PLASTIC; TEMPERATURE RATING -30 TO 55 DEG C; APPLICATION INDUSTRIAL; APPLICABLE STANDARD ANSI/NEDA, EPA
Product Type	Lantern Battery

Manufacturer Information

Brand	Rayovac Corporation
GTIN	00012800223435
Manufacturers Part Number	944C
UPC	012800223435

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Lantern Heavy Duty



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

21415 North 15th Lane Suite 116
85027-0000, AZ Phoenix
Phone: 480-681-0668
Fax: 480-681-0669

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
--------	---

Package	12
---------	----

Weight Per each	0
-----------------	---