



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 9575H3C000 Relay-440V DPDT Series 30

Eaton Corp

Catalog Number	9575H3C000
Manufacturer	Eaton Corp
Description	Relay, 9575H Series 3000 Series, DPDT Contact Configuration, 3.12 In Overall Length, 2.5 In Overall Width, 2.25 In Overall Height, Panel Mount, 50 to 60 HZ, 0.69 LB
Weight per unit	0.6800 (lbs/each)
Product Category	General Purpose Power Relays

### Features

Coil Voltage	440/480V
Contact Configuration	RIGID CONDUIT ELBOW, STANDARD RADIUS TYPE; STEEL MATERIAL; HOT-DIP GALVANIZED, BLUE URETHANE 2 MIL COATED INTERIOR, PVC 40 MIL COATED EXTERIOR FINISH; UL, CSA APPROVAL; 5 INCH TRADE SIZE; THREADED END TYPE; 22-1/2 DEG BEND ANGLE; 24 INCH BEND RADIUS
dimensions	79.2480millimetreX63.5000millimetreX57.1500millimetre

### Descriptions

Description	RELAY-440V DPDT SERIES 30
-------------	---------------------------

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114785751
UPC	782114785751

### Taxonomies, Classifications, and Categories

Category Description	GENERAL PURPOSE RELAYS
igcc	5359
unspsc code	39122325

### Packaging

Carton	1
Weight Per each	0.68

### Uses, Certifications, and Standards

Mounting	PANEL
standard	UL Listed file E1491;EN 60947-5-1;CSA file No. 41729



Powering Business Worldwide

pe.eaton.com

## 9575H Series 3000 Type AA General Purpose Relay

9575H3C000

UPC:782114785751

### Dimensions:

- **Height:** 2.25 IN
- **Length:** 3.12 IN
- **Width:** 2.5 IN

**Weight:** .69 LB

**Notes:** There are no "repair parts" available for these relays.

### Warranties:

- 1 year

### Specifications:

- **Coil Voltage:** 440/480V
- **Contact Configuration:** DPDT
- **Frequency Rating:** 50-60 Hz
- **Mounting:** Panel
- **Series:** 9575H Series 3000

### Supporting documents:

- [Eaton's Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 9575H3C000](#)

### Certifications:

- UL Listed file E1491
- CSA file No. 41729
- EN 60947-5-1

**Product compliance:** No Data

