



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A10106CH 10X10X6 N12 CH W/CLMPS

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | A10106CH |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Continuous Hinge Enclosure Clamps CH Type 12, 10X10X6, Gray, Mild Steel |
| Weight per unit | 48.0 (lbs/each) |
| Product Category | Nema Types 12 & 13 Metallic En |

Features

| | |
|-----------|------------------|
| ip rating | IP65 |
| Material | Mild Steel:Steel |

Material, Color, and Finish

| | |
|------------|---------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Powder Coated |

Dimensions and Weight

| | |
|-------|---------------------|
| Size | 10.00x10.00x6.00 in |
| Width | 10 |

Descriptions

| | |
|------------------------|--|
| Description | 10X10X6 N12 CH W/CLMPS |
| extra long description | NVENT HOF A10106CH CH Box 10.00x10. |
| Features | This easy-to-open, continuous hinge enclosure features screw-down clamps for secure closure and can be used in a wide variety of applications. |
| Long Description | Continuous Hinge Enclosure Clamps CH Type 12, 10x10x6, Gray, Mild Steel |
| Product Type | CH Box 10.00X10.00X6.00 |
| Short Description | CH Box 10.00x10.00x6.00 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510548803 |
| Manufacturers Part Number | A10106CH |
| UPC | 783510548803 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL JUNCTION BOXES |
| Type | Mild Steel Terminal and Junction Boxes |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 48 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------|
| Application | Controls and Drives |
| nema rating | 12 |