

# Specifications

## Eaton A201106-8

Eaton Crouse-Hinds series Roughneck E1049 plug insulator, Up to 1135A continuous, 313-777 kcmil, Brown, Hexagon crimp or solder, Male, Rubber, 1000 Vac/dc



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Roughneck E1049 plug insulator
<b>CATALOG NUMBER</b>	A201106-8
<b>UPC</b>	662275107350
<b>PRODUCT LENGTH/DEPTH</b>	11 in
<b>PRODUCT HEIGHT</b>	3.38 in
<b>PRODUCT WIDTH</b>	3.85 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>PRODUCT TYPE</b>	Plug insulator



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEMA RATING</b>	3

## Resources

<b>BROCHURES</b>	<a href="#">Roughneck Single Pole High-amperage Plugs and Connectors brochure</a>
<b>CATALOGS</b>	<a href="#">Roughneck Single Pole High Amperage Plugs and Connectors catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Eaton Bussmann EU Declaration of conformity 93-68-EEC2617</a>
<b>INSTALLATION INSTRUCTIONS</b>	<a href="#">IF 1778 - Roughneck E1049 Series Connectors and Receptacles</a> <a href="#">IF 1777 - Roughneck E1049 Series Connectors</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - A201106-8</a>

## Product specifications

<b>CABLE SIZE</b>	313-777 kcmil
<b>AMPERAGE RATING</b>	Up to 1135A Continuous
<b>VOLTAGE RATING</b>	1000 Vac/dc
<b>GENDER</b>	Male
<b>CONNECTION TYPE</b>	Hexagon crimp or solder
<b>COLOR</b>	Brown
<b>MATERIAL</b>	Rubber

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

