



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A51BAN1 1" Blue Ent 750' Reel

Cantex, Inc

Catalog Number	A51BAN1
Manufacturer	Cantex, Inc
Description	Cantex A51BAN1 Is A 1 In. X 750 FT. Reel Blue Ez-Flex Flexible Ent Electrical Nonmetallic Tubing Which Is A High Performance Low Cost Alternative to Electrical Metallic Tubing.
Weight per unit	N/A
Product Category	Conduit & Raceways

### Features

Inside Diameter	.999:1.059
outside diameter	1.305
Voltage Rating	600 V Max

### Material, Color, and Finish

Color	Blue
-------	------

### Dimensions and Weight

Length	9000
Size	1 in. x 750 ft. reel Blue EZ-Flex Flexible ENT Electrical Nonmetallic Tubing

### Descriptions

Description	1" BLUE ENT 750' REEL
extra long description	CTX A51BAN1 1 EZ FLEX 750' REEL
Features	CANTEX A51BAN1 is a 1 in. x 750 ft. reel Blue EZ-Flex Flexible ENT Electrical Nonmetallic Tubing which is a high performance low cost alternative to electrical metallic tubing.
Long Description	CANTEX A51BAN1 is a 1 in. x 750 ft. reel Blue EZ-Flex Flexible ENT Electrical Nonmetallic Tubing which is a high performance low cost alternative to electrical metallic tubing.
Product Type	1 Ez Flex 750' Reel

### Manufacturer Information

Brand	PVC & Accessories
GTIN	00088700961715
Manufacturers Part Number	A51BAN1
UPC	088700961715

### Taxonomies, Classifications, and Categories

Category Description	PVC & ENT
Type	EZ-Flex Flexible ENT Electrical Nonmetallic Tubing;Flexible ENT Electrical Nonmetallic Tubing



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Trade Size ..... 1

## Packaging

Carton ..... 750

Weight Per foot ..... 0

## Uses, Certifications, and Standards

Application ..... Flexible ENT Electrical Nonmetallic Tubing

standard ..... ETL Listed