

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street 66046-0000, KS Lawrence Phone: 785-330-9441 Fax: 785-371-0291



A512H 12 Hour Twist Timer Ivory *Nsi Industries*

Catalog Number	A512H
Manufacturer	Nsi Industries
Description	The Tork A512H 12-Hour Spring-Wound In-Wall Twist Timer Is Designed to Control A Variety Of Indoor Appliances and Lights. Automate Your Home or Office to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Features A Time Range Of 30 Minutes to 12 Hours, Plus It Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For Indoor Loads Such As Lights, Whole House Fans, Air Compressors, Water Heaters or Motors.
Weight per unit	0.3240 (lbs/each)
Product Category	Electromechanical Time Switche
Features	
action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	12 Hour
Dimensions and Weight Size	H=5.00 - W=3.00



Descriptions

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street 66046-0000, KS Lawrence Phone: 785-330-9441

Fax: 785-371-0291

Description	12 HOUR TWIST TIMER IVORY
extra long description	TORK A512H Interval Timer 12 Hr Hol
Features	The TORK A512H spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applicat
Long Description	The TORK A512H 12-Hour Spring-Wound In-Wall Twist Timer is designed to control a variety of indoor appliances and lights. Automate your home or office to save energy and money using the simple twist knob and reliable mechanical timekeeping. Features a time range of 30 minutes to 12 hours, plus it fits into a standard electrical box for in-wall mounting. Designed for indoor

heaters or motors.

Product Type Interval Timer 12 HR Hold White

Special Features Ivory 12 Hour No Hold In Wall Time Switch

loads such as lights, whole house fans, air compressors, water

Manufacturer Information

Brand	NSi	
GTIN	00786261150196	
Manufacturers Part Number	A512H	
UPC	786261150196	

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Туре	Spring Wound In Wall Time Switch

Packaging

Carton	1	
Weight Per each	0.324	



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

600 E 23rd Street 66046-0000, KS Lawrence Phone: 785-330-9441 Fax: 785-371-0291

Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus