



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ADR6034 60A 3W4P P&S Recpt (600VAC/250VDC)

Appleton/Oz Gedney

Catalog Number	ADR6034
Manufacturer	Appleton/Oz Gedney
Description	Powertite Grounding Style 2 Receptacle, Number Of Poles: 4, Number Of Wires: 3, Wire Size: 6 - 2 Awg (Building), 6 - 4 Awg (Extra Flex), Amperage Rating: 60 Amp, Voltage Rating: 600 Vac At 50 - 400 HZ, 250 VDC, Phase: 3 PH, Material: Copp
Weight per unit	3.0 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	60
connection	Pressure Wire Terminal
Material	Copperfree (4/10 Of 1 PCT Maximum) Aluminum
Number of Wires	3
Phase	3
Poles	4
Voltage Rating	600 VAC At 50 - 400 HZ, 250 VDC
Wire Size	6 - 2 AWG (Building), 6 - 4 AWG (Extra Flex)

Descriptions

Description	60A 3W4P P&S RECPT (600VAC/250VDC)
extra long description	APP ADR6034 60A RECPT 4PS2 SCR/SPRG
Long Description	Powertite Grounding Style 2 Receptacle, Number Of Poles: 4, Number Of Wires: 3, Wire Size: 6 - 2 AWG (Building), 6 - 4 AWG (Extra Flex), Amperage Rating: 60 AMP, Voltage Rating: 600 VAC At 50 - 400 HZ, 250 VDC, Phase: 3 PH, Material: Copp
Product Type	60A Recpt 4PS2 SCR/SPRG CVRS
Special Features	Designed to supply power to portable or fixed electrical equipment such as motor generator units, welders, pumps, compressors, cellular relay stations and similar apparatus;Grounding style: Shell and extra pole;Ideal for use on shipping docks, ports and other ship to shore applications;Natural finish glass filled polyester insulating blocks;Receptacle is NEMA 4X rated when screw cap is closed when the receptacle is not in use;Rough usage construction;Suitable for use in locations where a weatherproof enclo



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Appleton
GTIN	00781381186421
Manufacturers Part Number	ADR6034
UPC	781381186421

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 2 Receptacle

Packaging

Carton	6
Weight Per each	3

Uses, Certifications, and Standards

Application	For ACP6034BC Metallic And NMACP6034BC Nonmetallic Clamping Ring Plugs
Mounting	BOX
nema rating	NEMA 3, 3R, 4, 4X
standard	CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917