



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832



ABM2SS6D 1X1 4WAY WHT Screw CBL Tie MNT *Panduit Corporation*

Catalog Number	ABM2SS6D
Manufacturer	Panduit Corporation
Description	Panduit'S ABM2S-S6-D 4-Way Cable Tie Mounts Allow Cable Tie Entry From All Four Sides. They Can Easily Be Applied With User Supplied Adhesive or Size #6 (M3) Screws. They Are Made Of Abs Plastic and Designed For Indoor Use. Used With Miniature, Intermediate and Standard Cable Ties. They Are 1.0" X 1.0" (25.4MM X 25.4MM), Are White In Color and Come In Packages Of 500.
Weight per unit	1.5 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Other
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	1X1 4WAY WHT SCREW CBL TIE MNT
extra long description	PAN ABM2S-S6-D ABM2S-S6-D Cable Tie
Long Description	Panduit's ABM2S-S6-D 4-Way Cable Tie Mounts allow cable tie entry from all four sides. They can easily be applied with user supplied adhesive or size #6 (M3) screws. They are made of ABS Plastic and designed for indoor use. Used with miniature, intermediate and standard cable ties. They are 1.0" x 1.0" (25.4mm x 25.4mm), are white in color and come in packages of 500.
Product Type	ABM2S-S6-D Cable Tie Mount, White, Abs, Screw, 1X1", PK500

Manufacturer Information

Brand	Panduit®
GTIN	00074983580569
Manufacturers Part Number	ABM2S-S6-D
UPC	074983580569

Taxonomies, Classifications, and Categories

Type	Cable Tie Mount
------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy
75701-0000, TX Tyler
Phone: 903-509-9882
Fax: 903-509-9832

Availability

minimum qty 500

Packaging

Carton 500

Package 1000

Weight Per each 1.45

Uses, Certifications, and Standards

Application Indoor;Used with Miniature, Intermediate, and Standard Cables
Ties

Mounting Screw-on

standard CE Compliant, UL Recognized: E136577, RoHS Compliant