



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue  
64120-0000, MO Kansas City  
Phone: 913-227-4257  
Fax: 816-656-2196



## AE110L 110 CFM 1.3 Sones Led Fan/Light

Broan/Nutone LLC

Catalog Number	AE110L
Manufacturer	Broan/Nutone LLC
Description	Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UI, Hvi Approval; 120 Volt At 60 Hertz Voltage Rating; 0.3 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage
Weight per unit	9.1 (lbs/each)
Product Category	Exhaust Fans

### Features

Air Flow Rate	110 CFM
Current Rating	0.3 Amp
Duct Shape	Round
Duct Size	4 Inch Diameter
Grill Finish	White Polymeric
Grill Shape	Rectangular
Grill Size	11-3/4 Inch Length x 12-1/2 Inch Width
Housing Shape	Rectangular
Lamp Included	Yes
Lamp Type	LED
Lamp Wattage	11 Watt
Sound Level	1.3 SONES
Ventilation Area	105 Square Foot
Voltage Rating	120 Volt at 60 Hertz

### Material, Color, and Finish

Housing Material	Rugged 26 Gauge Galvanized Steel
------------------	----------------------------------

### Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue  
64120-0000, MO Kansas City  
Phone: 913-227-4257  
Fax: 816-656-2196

## Descriptions

Additional Information

Power Rating 23.4 Watt; Number of Speed 1; Includes Permanently Lubricated Plug-In Motor, Tapered Sleeve, Non-Metallic Damper; Excludes Metallic Clatter; Standard Package 1 per pack

Commodity Description

Exhaust Fans

Description

110 CFM 1.3 SONES LED FAN/LIGHT

extra long description

CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; RUGGED 26 GAUGE GALVANIZED STEEL HOUSING MATERIAL; 110 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.3 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE POLYMERIC GRILL FINISH; 105 SQUARE FOOT VENTILATION

Long Description

BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT AT 60 HERTZ VOLTAGE RATING; 0.3 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE

Product Type

Bath Fan and Light

## Manufacturer Information

Brand

Broan/Nutone LLC

GTIN

00026715236664

Manufacturers Part Number

AE110L

UPC

026715236664

## Taxonomies, Classifications, and Categories

Category Description

FANS & HEATERS

Type

CEILING

## Packaging

Carton

1

Weight Per each

9.07

## Uses, Certifications, and Standards

Approval

UL, HVI