



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

700 Industry Way Suite 10
75078-0000, TX Prosper
Phone: 469-899-3981
Fax: 469-899-3982



AGC15R 15A 32VAC Non Indicating Glass Fast Acting Fuse

Bussmann Fuses

Catalog Number	AGC15R
Manufacturer	Bussmann Fuses
Description	Eaton MDQ Series Duel-Element, Time-Delay Fuse, 10A, 32 Vac, V-10
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	15
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	1 kAIC at 32 Vac
Material	Glass Fuse;Nickel-plated brass end cap construction
Response Time	60 min at 135%, 120 sec at 200%
Voltage Rating	32 Vac, 32 Vdc (self certified)

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	15A 32VAC NON INDICATING GLASS FAST ACTING FUSE
extra long description	BUSS AGC-15-R BUSS SMALL DIMENSION
Features	Fast-acting, glass tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's AGC fast-acting, glass tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase w
Long Description	Eaton MDQ Series Duel-element, Time-delay fuse, 10A, 32 Vac, V-10
Product Type	Buss Small Dimension Fuse
Special Features	Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Compliant

Manufacturer Information

Brand	Eaton
GTIN	00051712655026
Manufacturers Part Number	AGC-15-R
UPC	051712655026



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

700 Industry Way Suite 10
75078-0000, TX Prosper
Phone: 469-899-3981
Fax: 469-899-3982

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	1?4" x 1 1?4" 3AG Fast-acting glass tube fuse

Packaging

Carton	1
Package	5
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked,RoHS Compliant