## Specifications







## Eaton AGC-6-R

Eaton ABC series Fast-acting fuse, 30A, 250 Vac, 125 Vdc, 32 Vac (self certified)

General specifications		
PRODUCT NAME	Eaton Bussmann series AGC 1/4" x 1 1/4" 3AG Fast- acting glass tube fuse	
CATALOG NUMBER	AGC-6-R	
UPC	051712655248	
PRODUCT LENGTH/DEPTH	1.25 in	
PRODUCT HEIGHT	0.25 in	
PRODUCT WIDTH	0.25 in	
PRODUCT WEIGHT	0.004 lb	
WARRANTY	Not Applicable	
COMPLIANCES	RoHS Compliant CE Marked	



Product specifications		
USED WITH	out axial leads	
AMPERAGE RATING	6 A	
INTERRUPT RATING	200 AIC at 250 Vac 10 kAIC at 125 Vac	
FUSE INDICATOR	Non-indicating	
CONNECTION	Ferrule end x ferrule end	
RESPONSE TIME	60 min at 135%, 120 sec at 200%	
MATERIAL	Glass tube Nickel-plated brass end cap construction	
QUANTITY	5	
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)	
ТҮРЕ	Electronic	
APPLICATION	Electronic circuits	

Resources	
SPECIFICATIONS AND	<u>Eaton Specification Sheet -</u> <u>AGC-6-R</u>
DATASHEETS	Eaton AGC fast-acting glass tube fuses data- sheet

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc** Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com



information.



latest product and support

Follow us on social media to get the





## Specifications







## Eaton AGC-6-R

Eaton ABC series Fast-acting fuse, 30A, 250 Vac, 125 Vdc, 32 Vac (self certified)

General specifications		
PRODUCT NAME	Eaton Bussmann series AGC 1/4" x 1 1/4" 3AG Fast- acting glass tube fuse	
CATALOG NUMBER	AGC-6-R	
UPC	051712655248	
PRODUCT LENGTH/DEPTH	1.25 in	
PRODUCT HEIGHT	0.25 in	
PRODUCT WIDTH	0.25 in	
PRODUCT WEIGHT	0.004 lb	
WARRANTY	Not Applicable	
COMPLIANCES	RoHS Compliant CE Marked	



Product specifications		
USED WITH	out axial leads	
AMPERAGE RATING	6 A	
INTERRUPT RATING	200 AIC at 250 Vac 10 kAIC at 125 Vac	
FUSE INDICATOR	Non-indicating	
CONNECTION	Ferrule end x ferrule end	
RESPONSE TIME	60 min at 135%, 120 sec at 200%	
MATERIAL	Glass tube Nickel-plated brass end cap construction	
QUANTITY	5	
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)	
ТҮРЕ	Electronic	
APPLICATION	Electronic circuits	

Resources	
SPECIFICATIONS AND	<u>Eaton Specification Sheet -</u> <u>AGC-6-R</u>
DATASHEETS	Eaton AGC fast-acting glass tube fuses data- sheet

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc** Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com



information.



latest product and support

Follow us on social media to get the



