

Specifications



Eaton AH5266

Eaton Arrow Hart ultra grip straight blade plug, #18 - #12 AWG, 15A, Industrial, 125V, Back wire, Black, Brass, Nylon, 5-15P, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Arrow Hart ultra grip straight blade plug |
| CATALOG NUMBER | AH5266 |
| UPC | 032664737503 |
| PRODUCT LENGTH/DEPTH | 2.23 in |
| PRODUCT HEIGHT | 2.1 in |
| PRODUCT WIDTH | 2.59 in |
| PRODUCT WEIGHT | 0.17 lb |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | cULus Listed NOM Federal Specification Classification W-C-596F |
| PRODUCT TYPE | Ultra grip |



Powering Business Worldwide

Electrical Ratings

| | |
|--------------------|-------------|
| AMPERAGE RATING | 15A |
| NEMA CONFIGURATION | 5-15P |
| TORQUE RATING | 14 lbf-inch |
| VOLTAGE RATING | 125V |
| WIRING METHOD | Back wire |

Product Specifications

| | |
|---------------------|---|
| ALLOWABLE WIRE SIZE | #18-12 AWG |
| APPLICATION | Industrial |
| CONNECTION TYPE | Screw |
| CORD RANGE | 0.33-0.66" in diameter |
| DESIGN TYPE | Straight blade |
| DEVICE GRADE | Extra heavy-duty industrial specification grade |
| DEVICE TYPE | Plug |
| NUMBER OF POLES | Two-pole |
| NUMBER OF WIRES | 3 |
| RECEPTACLE TYPE | Two-pole, three-wire, grounding |
| STYLE TYPE | Straight body |
| TYPE | Plug |

Material Specifications

| | |
|--------------------|-----------|
| COLOR | Black |
| CONTACT MATERIAL | Brass |
| FACE/BODY MATERIAL | Nylon |
| MATERIAL | Nylon |
| PACKAGING TYPE | Core pack |

Resources

| | |
|-------------------------------|--|
| MULTIMEDIA | Arrow Hart - Connecting Safety to Reliability since 1890 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - AH5266 Industrial Grade Straight Blade Devices Spec Sheet |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton AH5266

Eaton Arrow Hart ultra grip straight blade plug, #18 - #12 AWG, 15A, Industrial, 125V, Back wire, Black, Brass, Nylon, 5-15P, Two-pole, three-wire, grounding, Screw, 0.33-0.66", Nylon, Core pack

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Arrow Hart ultra grip straight blade plug |
| CATALOG NUMBER | AH5266 |
| UPC | 032664737503 |
| PRODUCT LENGTH/DEPTH | 2.23 in |
| PRODUCT HEIGHT | 2.1 in |
| PRODUCT WIDTH | 2.59 in |
| PRODUCT WEIGHT | 0.17 lb |
| COMPLIANCES | RoHS Compliant |
| CERTIFICATIONS | cULus Listed NOM Federal Specification Classification W-C-596F |
| PRODUCT TYPE | Ultra grip |



Powering Business Worldwide

Electrical Ratings

| | |
|--------------------|-------------|
| AMPERAGE RATING | 15A |
| NEMA CONFIGURATION | 5-15P |
| TORQUE RATING | 14 lbf-inch |
| VOLTAGE RATING | 125V |
| WIRING METHOD | Back wire |

Product Specifications

| | |
|---------------------|---|
| ALLOWABLE WIRE SIZE | #18-12 AWG |
| APPLICATION | Industrial |
| CONNECTION TYPE | Screw |
| CORD RANGE | 0.33-0.66" in diameter |
| DESIGN TYPE | Straight blade |
| DEVICE GRADE | Extra heavy-duty industrial specification grade |
| DEVICE TYPE | Plug |
| NUMBER OF POLES | Two-pole |
| NUMBER OF WIRES | 3 |
| RECEPTACLE TYPE | Two-pole, three-wire, grounding |
| STYLE TYPE | Straight body |
| TYPE | Plug |

Material Specifications

| | |
|--------------------|-----------|
| COLOR | Black |
| CONTACT MATERIAL | Brass |
| FACE/BODY MATERIAL | Nylon |
| MATERIAL | Nylon |
| PACKAGING TYPE | Core pack |

Resources

| | |
|-------------------------------|--|
| MULTIMEDIA | Arrow Hart - Connecting Safety to Reliability since 1890 |
| SPECIFICATIONS AND DATASHEETS | Eaton Specification Sheet - AH5266 Industrial Grade Straight Blade Devices Spec Sheet |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

