



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902



AGC134R 1-3/4A 250V 1/4X1-1/4 Rohs Fa Glass Fuse *Bussmann Fuses*

Catalog Number	AGC134R
Manufacturer	Bussmann Fuses
Description	Eaton Agc Series Fast-Acting Fuse 1.75A, 250 Vac, 32 VDC (Self Certified), Agc-1-3-4-R
Weight per unit	0.0300 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	1.75
connection	Ferrule End X Ferrule End
dimensions	1.2500 IN X 0.2500 IN X 0.2500 IN
interrupt rating	100 AIC at 250 Vac10 kAIC at 125 Vac
Material	Glass Fuse;Nickel-plated brass end cap construction
Response Time	60 min at 135%, 120 sec at 200%
Voltage Rating	250 Vac, 32 Vdc (self certified)

Descriptions

Description	1-3/4A 250V 1/4X1-1/4 ROHS FA GLASS FUSE
extra long description	BUSS AGC-1-3/4-R BUSS SMALL DIMENSI
Features	Fast-acting, glass tube 1/4" x 1-1/4" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation. Eaton's AGC fast-acting, glass tube 1/4" x 1-1/4" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase w
Long Description	Eaton AGC series Fast-acting fuse 1.75A, 250 Vac, 32 Vdc (self certified), AGC-1-3-4-R
Product Type	Buss Small Dimension Fuse

Manufacturer Information

Brand	Eaton
GTIN	00051712654852
Manufacturers Part Number	AGC-1-3/4-R
UPC	051712654852

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	1/4" x 1 1/4" 3AG Fast-acting glass tube fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902

Packaging

Carton	5
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked, RoHS Compliant