Specifications







Eaton AGC-2-R

Eaton MDQ Series Duel-element, Time-delay fuse, 1A, 250 Vac, 32 Vdc (self certified), MDQ

General specification	าร
PRODUCT NAME	Eaton Bussmann series AGC fast-acting glass tube fuse
CATALOG NUMBER	AGC-2-R
UPC	051712655057
PRODUCT LENGTH/DEPTH	1.25 in
PRODUCT HEIGHT	0.25 in
PRODUCT WIDTH	0.25 in
PRODUCT WEIGHT	0.004 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant



Product specifications		
USED WITH	out axial leads	
AMPERAGE RATING	2 A	
INTERRUPT RATING	100 AIC at 250 Vac 10 kAIC at 125 Vac	
FUSE INDICATOR	Non-indicating	
CONNECTION	Ferrule end x ferrule end	
RESPONSE TIME	60 min at 135%, 120 sec at 200%	
MATERIAL	Glass tube Nickel-plated brass end cap construction	
QUANTITY	5	
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)	
ТҮРЕ	Electronic	
APPLICATION	Electronic circuits	

SPECIFICATIONS AND DATASHEETS Eaton Specification Sheet AGC-2-R Eaton AGC fast-acting glass tube fuses data- sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

 $\hbox{@ 2025 Eaton.}$ All Rights Reserved.

Follow us on social media to get the latest product and support information.











Specifications







Eaton AGC-2-R

Eaton MDQ Series Duel-element, Time-delay fuse, 1A, 250 Vac, 32 Vdc (self certified), MDQ

General specification	าร
PRODUCT NAME	Eaton Bussmann series AGC fast-acting glass tube fuse
CATALOG NUMBER	AGC-2-R
UPC	051712655057
PRODUCT LENGTH/DEPTH	1.25 in
PRODUCT HEIGHT	0.25 in
PRODUCT WIDTH	0.25 in
PRODUCT WEIGHT	0.004 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant



Product specifications		
USED WITH	out axial leads	
AMPERAGE RATING	2 A	
INTERRUPT RATING	100 AIC at 250 Vac 10 kAIC at 125 Vac	
FUSE INDICATOR	Non-indicating	
CONNECTION	Ferrule end x ferrule end	
RESPONSE TIME	60 min at 135%, 120 sec at 200%	
MATERIAL	Glass tube Nickel-plated brass end cap construction	
QUANTITY	5	
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)	
ТҮРЕ	Electronic	
APPLICATION	Electronic circuits	

SPECIFICATIONS AND DATASHEETS Eaton Specification Sheet AGC-2-R Eaton AGC fast-acting glass tube fuses data- sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

 $\hbox{@ 2025 Eaton.}$ All Rights Reserved.

Follow us on social media to get the latest product and support information.









