



AHMC260L Man Cont 2POS DPST 60A 600VAC Box Lug BK

Eaton Wiring Devices

Catalog Number	AHMC260L
Manufacturer	Eaton Wiring Devices
Description	Eaton Manual Motor Controller, Switch Only, #14-4 Awg, 60A, Industrial, Panel, 600V, Side Wired Box Lug, Maintained Contact, Black, Open, Two-Pole, Single-Phase, Toggle Switch, Copper-Alloy Terminal, Single-Throw, Glass-Filled Nylon
Weight per unit	N/A
Product Category	Disconnect Motor Switches

Features

amperage rating	60A
dimensions	1.7600 IN X 2.3400 IN X 4.3300 IN
Poles	Two-pole
Voltage Rating	600 V

Descriptions

Description	MAN CONT 2POS DPST 60A 600VAC BOX LUG BK
extra long description	EWD AHMC260L Man Cont 2Pos DPST 60A
Features	Eaton's Arrow Hart manual motor controllers offer compact, industrial-grade designs built to provide safe, reliable motor control performance in even the most rugged environments. They feature high-impact-resistant, glass-filled nylon construction; easy-to-read electrical ratings on rugged steel mounting straps; clear ON/OFF indicators on large, rugged toggles; distinct wire pockets and thick-wall arc barriers to contain strands; and screw-and-clamp or box-lug terminals to meet individual project requireme
Long Description	Eaton manual motor controller, Switch only, #14-4 AWG, 60A, Industrial, Panel, 600V, Side wired box lug, Maintained contact, Black, Open, Two-pole, Single-phase, Toggle switch, Copper-alloy terminal, Single-throw, Glass-filled nylon
Product Type	Man Cont 2POS DPST 60A 600VAC Box Lug BK
Special Features	Switch only

Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00040893653846
Manufacturers Part Number	AHMC260L
UPC	040893653846



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1722 Primewest Parkway
77449-0000, TX Katy
Phone: 281-828-2012
Fax: 281-828-2512

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous commercial & industrial devices
Type	Manual motor controller

Packaging

Carton	1
Package	10
Weight Per each	0

Uses, Certifications, and Standards

Application standard	Ind Facilities & Factories - Facility - Other cULus Listed,NAFTA,RoHS Compliant
----------------------	--