



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **AL600N 600 MCM Al/Cu Crimp** *Nsi Industries*

Catalog Number	AL600N
Manufacturer	Nsi Industries
Description	2HOLESTANDARD Barrelaluminum Compression Lug 600 MCM -1/2 Bolt Standard Barrelaluminum Compression Lugs Is A Type Ofaluminum Compression Connector That Is Produced From High Conductivityaluminum Tubing.Center Stop Assures Proper Cable Installation.They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.6400 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Cable Size	600 MCM (STR)
Material	Aluminum
Number of Holes	2
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

### **Material, Color, and Finish**

Color	Black
Finish	Tin Plated Bronze

### **Dimensions and Weight**

Size	L=6.74 - W=1.95 - OD=1.44 = ID=.920
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	600 MCM AL/CU CRIMP
extra long description	NSI AL600N 1x500-4 LINE 6x2/0-14 LO
Features	2HoleStandard BarrelAluminum Compression Lug 600 MCM -1/2 Bolt Standard BarrelAluminum Compression Lugs is a type ofaluminum compression connector that is produced from high conductivityaluminum tubing.Center stop assures proper cable installation.They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2HoleStandard BarrelAluminum Compression Lug 600 MCM -1/2 Bolt Standard BarrelAluminum Compression Lugs is a type ofaluminum compression connector that is produced from high conductivityaluminum tubing.Center stop assures proper cable installation.They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	1X500-4 Line 6X2/0-14 Load
Special Features	600 MCM (STR) - 1/2 Mounting Holes - 1 3/4 Hole Spacing

## Manufacturer Information

Brand	NSi
GTIN	00662381031099
Manufacturers Part Number	AL600N
sub brand	Aluminum Compression
UPC	662381031099

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel - Two Hole

## Packaging

Carton	1
Package	3
Weight Per each	0.64

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Holes
standard	UL486A/B