



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AL9V6J 9V Ultrapro Alk Bty 6PK

Rayovac Corporation

Catalog Number	AL9V6J
Manufacturer	Rayovac Corporation
Description	Alkaline Battery, 9V Alkaline Battery Battery Type, Alkaline Chemistries Type, 9 V Input Voltage Rating, 6 CT;72 PK Package Quantity
Weight per unit	N/A
Product Category	Batteries & Chargers

Features

Voltage Rating	9 Volt
----------------	--------

Dimensions and Weight

Height	1.831 to 1.909 Inch
Width	0.965 to 1.043 Inch

Descriptions

Additional Information	Temperature Rating -20 to 130 Deg F; Volume 1.2 Cubic Inch; Applicable Standard ANSI/NEDA/IEC, EPA
Commodity Description	Flashlts & Batts - Batteries & Chargers
Description	9V ULTRAPRO ALK BTY 6PK

Manufacturer Information

GTIN	00012800000449
UPC	012800000449

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	ALKALINE

Availability

minimum qty	6
-------------	---

Packaging

Carton	6
Package	72
Standard Package	6 Unit per Pack
Weight Per battery	0

Uses, Certifications, and Standards

Application	Photo Flash, Lighting, Toy, Tape/Audio, Remote, Radio
-------------	---

Stock Number/ SKU	Description	Mfg. UPC	Pack Dimensions	Case UPC	Case Dimensions	Batteries/ Case	Case Qty.	Case Wt.	Case Cu. Ft.
INDUSTRIAL CONTRACTOR PACK BATTERIES									
ALAA-24	Alkaline Reclosable AA-24 Pack	12800474097	3.19 x 4.19 x 2.13	10012800474094	9.75 x 9.25 x 4.38	288	12	15.68	0.20
ALAA-48	Alkaline Reclosable AA-48 Pack	12800503889	5.25 x 4.13 x 2.13	10012800503886	11 x 8.56 x 4.88	384	8	21.28	0.27
ALAAA-18	Alkaline Reclosable AAA-18 Pack	12800474103	2 x 3.19 x 1.75	10012800474100	7.31 x 6.5 x 4	216	12	6.00	0.11
ALAAA-24	Alkaline Reclosable AAA-24 Pack	12800507986	1.75 x 2.38 x 3.19	10012800507983	7.63 x 7.38 x 3.88	288	12	7.86	0.13
ALC-12	Alkaline Reclosable C-12 Pack	12800474110	3.88 x 4.88 x 2	10012800474117	9.94 x 8.13 x 4.75	96	8	15.20	0.22
ALD-12	Alkaline Reclosable D-12 Pack	12800474127	4.81 x 6.13 x 2.38	10012800474124	12.63 x 10.06 x 6	96	8	30.88	0.44
AL9V-8	Alkaline Reclosable 9V-8 Pack	12800474080	2.94 x 3.63 x 2	10012800474087	9.38 x 8.25 x 4.38	96	12	10.80	0.20
AL9V-12	Alkaline Reclosable 9V-12 Pack	12800507832	4 x 3.69 x 2.06	10012800507839	12.31 x 8.25 x 4.38	144	12	15.48	0.26



INDUSTRIAL ALKALINE BATTERIES									
AL-AA	Alkaline Shrink-Wrapped AA-8 Pack	12800000432	0.5 x 4.5 x 2	10012800000439	8.63 x 5.13 x 1.75	96	12	5.28	0.05
AL-AAA	Alkaline Shrink-Wrapped AAA-8 Pack	12800000456	0.38 x 3 x 1.75	10012800000453	7.5 x 3.81 x 1.34	96	12	2.50	0.02
AL-C	Alkaline Shrink-Wrapped C-6 Pack	12800000418	1 x 6 x 2	10012800000415	8.88 x 6.88 x 3.25	72	12	11.40	0.12
AL-D	Alkaline Shrink-Wrapped D-6 Pack	12800000425	1.25 x 7.75 x 2.38	10012800000422	10.5 x 8.5 x 4.13	72	12	23.28	0.22
AL-9V	Alkaline Shrink-Wrapped 9V-6 Pack	12800000449	0.69 x 6 x 1.88	10012800000446	8.63 x 6.88 x 2.13	72	12	7.32	0.07
815 Bulk	Alkaline AA Size	12800173433	---	12800991556	14.44 x 13.38 x 3.75	500	---	27.00	0.42
824 Bulk	Alkaline AAA Size	12800194636	---	12800991570	11.25 x 9.5 x 2.88	500	---	14.00	0.18
814 Bulk	Alkaline C Size	12800177721	---	10012800177728	13.25 x 13.25 x 2.88	168	---	28.56	0.29
813 Bulk	Alkaline D Size	12800174676	---	10012800174673	13.25 x 13.25 x 2.88	105	---	34.65	0.29
813FT	Alkaline D Size, Flat Top	12800000005	---	10012800000002	14.5 x 13.63 x 3.25	105	---	34.23	0.37
A1604 BK210	Alkaline 9-Volt	12800236046	---	20012800236040	11.63 x 2.75 x 16.38	210	---	22.47	0.30



HEAVY DUTY BATTERIES									
HD-AA	Heavy Duty Shrink-Wrapped AA-8 Pack	12800000487	0.5 x 4.5 x 2	12800000890	8.63 x 5.13 x 1.75	96	12	4.32	0.05
HD-C	Heavy Duty Shrink-Wrapped C-6 Pack	12800000463	1 x 6 x 2	12800000852	8.88 x 6.88 x 3.25	72	12	8.40	0.12
HD-DA	Heavy Duty Shrink-Wrapped D-6 Pack	12800000470	1.25 x 7.75 x 2.38	12800000869	10.5 x 8.5 x 4.13	72	12	13.92	0.21
HD-9V	Heavy Duty Shrink-Wrapped 9V-6 Pack	12800000494	0.69 x 6 x 1.88	12800000906	8.63 x 6.88 x 2.13	72	12	6.36	0.07
3AAA-4	Heavy Duty Carded AAA-4 Pack	12800458714	0.5 x 3.75 x 4.5	20012800458718	7.63 x 5.88 x 4.13	96	24	2.40	0.11
3AAA-8CTA	Heavy Duty Carded AAA-8 Pack	12800507337	0.5 x 3.88 x 4.5	10012800507334	12.5 x 5.5 x 5.5	240	30	5.70	0.22
5AA Bulk	Heavy Duty AA Size	12800379866	---	12800993963	14.38 x 13.13 x 5.88	1000	---	43.00	0.64
6D Bulk	Heavy Duty D Size	12800379606	---	10012800379603	21 x 12.88 x 3.75	154	---	32.50	0.59



Battery Size	Stock Number/ SKU	Description	Mfg. UPC	Pack Dimensions	Case UPC	Case Dimensions	Batteries/ Case	Case Qty.	Case Wt.	Case Cu. Ft.
VARTA - ALKALINE HIGH ENERGY										
	V4906121412	Varta Alkaline High Energy AA 2-Pack	4008496559398	3.15 x 0.63 x 4.72	4008496559404	5.04 x 6.34 x 3.27	40	20	2.32	0.06
	V4906121414	Varta Alkaline High Energy AA 4-Pack	4008496559435	3.15 x 0.63 x 4.72	4008496559442	5.04 x 6.34 x 3.27	80	20	4.40	0.06
	V4903121412	Varta Alkaline High Energy AAA 2-Pack	4008496559701	3.15 x 0.47 x 4.72	4008496559718	5.91 x 6.97 x 3.27	20	10	0.69	0.08
	V4903121414	Varta Alkaline High Energy AAA 4-Pack	4008496559749	3.15 x 0.47 x 4.72	4008496559756	4.96 x 2.52 x 3.27	40	10	1.15	0.02
	V4914121412	Varta Alkaline High Energy C 2-Pack	4008496559312	3.15 x 1.06 x 4.72	4008496559329	5.24 x 5.47 x 3.27	20	10	2.92	0.05
	V4920121412	Varta Alkaline High Energy D 2-Pack	4008496559237	3.15 x 1.38 x 4.72	4008496559244	5.91 x 6.97 x 3.27	20	10	6.37	0.08
	V4922121411	Varta Alkaline High Energy 9V 1-Pack	4008496559862	3.15 x 0.75 x 4.72	4008496559879	5.59 x 3.7 x 3.27	10	10	1.24	0.04
	V4912121411	Varta Alkaline High Energy 4.5V 1-Pack	4008496559947	3.15 x .091 x 4.72	4008496559954	4.84 x 6.14 x 3.27	10	10	3.87	0.42
	V4761101412	Varta Alkaline High Energy AAAA 2 Pack	4008496524976	0.38 x 3.19 x 4.75	4008496524983	5.5 x 2.06 x 3.25	20	10	0.53	0.02
VARTA - ALKALINE HIGH ENERGY TRAY PACKS										
	V4903121111	Varta Alkaline AAA 10 Pillow Tray	4008496573448	---	4008496573462	9.65 x 4.06 x 2.36	200	---	5.20	0.05
	V4906121354	Varta Alkaline AA 4 Foil Wrap Tray	4008496573400	2.36 x 0.59 x 2.05	4008496573417	5.91 x 2.6 x 2.09	40	10	2.07	0.02
	V4914121111	Varta Alkaline C Tray	4008496573363	---	4008496573370	5.32 x 4.25 x 2.05	20	---	3.08	0.03
	V4920121111	Varta Alkaline D Tray	4008496573325	---	4008496573332	6.77 x 5.51 x 2.48	20	---	6.36	0.05
	V4922121111	Varta Alkaline 9V Tray	4008496573493	---	4008496573509	5.2 x 2.8 x 1.97	20	---	2.10	0.02
VARTA - ALKALINE HIGH ENERGY BULK PACKS										
	V4903121511	Varta Alkaline AAA Bulk	4008496575053	---	4008496575060	9.76 x 10.32 x 2.36	500	---	12.57	0.14
	V4906121511	Varta Alkaline AA Bulk	4008496574995	---	4008496575008	12.6 x 13.27 x 2.52	500	---	26.24	0.24
	V4922121501A	Varta Alkaline 9V Bulk	4008496575084	---	4008496634750	18.13 x 13 x 2.41	272	---	28.29	0.33
VARTA - RECHARGEABLE										
	V5703301402	Varta Rechargeable AAA 1000 mAh 2-Pack	4008496538621	3.15 x 0.47 x 4.72	4008496538638	5.43 x 2.48 x 3.23	20	10	0.78	0.03
	V5706301402	Varta Rechargeable AA 2700 mAh 2-Pack	4008496528509	3.15 x 0.63 x 4.72	4008496528516	3.15 x 4.98 x 3.29	20	10	1.30	0.03
	V56722101401	Varta Rechargeable 9V 200 mAh 1-Pack	4008496550814	3.15 x 0.75 x 4.72	4008496550821	5.5 x 3.63 x 3.13	10	10	1.25	0.04
VARTA - PHOTO ALKALINE										
	V4206201404	Varta Photo Alkaline AA 4-Pack	4008496369485	3.15 x 0.63 x 4.72	4008496369492	5.04 x 6.34 x 3.27	80	20	4.40	0.06
	V4203201404	Varta Photo Alkaline AAA 4-Pack	4008496369607	3.15 x 0.47 x 4.72	4008496369614	4.96 x 2.52 x 3.27	40	10	0.29	0.02
VARTA - PHOTO LITHIUM										
	V6205301401A	Varta Photo Lithium 3V, 123A 1-Pack	4008496537280	3.15 x 0.71 x 4.72	4008496537297	3.86 x 5 x 3.29	10	10	0.62	0.04
	V6205301402A	Varta Photo Lithium 3V, 123A 2-Pack	4008496537327	3.15 x 0.71 x 4.72	4008496537334	3.86 x 5 x 3.29	20	10	0.90	0.04
	V6204301401A	Varta Photo Lithium 6V, CRP2 / 223 1-Pack	4008496537242	3.15 x 0.79 x 4.72	4008496537259	4.29 x 5 x 3.29	10	10	1.08	0.04

