



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253



ASC10T 1/0 Alum Comp. Butt Splic

Nsi Industries

Catalog Number	ASC10T
Manufacturer	Nsi Industries
Description	Dual Rated Aluminum Splice 1/0 Awg Dual Rated Aluminum Splices Are A Type Of Aluminum Compression Connector That Is Produced From High Conductivity Aluminum Tubing. Center Stop Assures Proper Cable Installation. Electro-Tin Plated For Corrosion Resistance. Color Coded and Marked With Die Index Information. Pre-Filled With Oxide Inhibitor and Capped With Color Coded Cap.
Weight per unit	0.0400 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Material	Aluminum
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Tan
Finish	Tin Plated Bronze

Dimensions and Weight

Size	L=2.50 - OD=.629 - ID=.389
------	----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253

Descriptions

Description	1/0 ALUM COMP. BUTT SPLIC
extra long description	NSI ASC1/0T 1/0 AWG Aluminum Splice
Features	Dual Rated Aluminum Splice 1/0 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Long Description	Dual Rated Aluminum Splice 1/0 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap.
Product Type	1/0 Awg Aluminum Splice - Dual Rated - Tan
Special Features	1/0 AWG (STR) - ALCU Splice

Manufacturer Information

Brand	NSi
GTIN	00662381032041
Manufacturers Part Number	ASC1/0T
UPC	662381032041

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel - ALCU Splice

Packaging

Carton	1
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B
Temperature Rating	90 C