ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10524 W US Hwy 80
75126-0000, TX Forney
Phone: 972-210-2783
Fax: 972-210-2784



# ASC20T 2/0 Al/Cu Compression Butt Splice

*Nsi Industries*

| | |
|---|---|
| Catalog Number | ASC20T |
| Manufacturer | Nsi Industries |
| Description | Dual Rated Aluminum Splice 2/0 Awg Dual Rated Aluminum Splices Are A Type Of Aluminum Compression Connector That Is Produced From High Conductivity Aluminum Tubing. Center Stop Assures Proper Cable Installation. Electro-Tin Plated For Corrosion Resistance. Color Coded and Marked With Die Index Information. Pre-Filled With Oxide Inhibitor and Capped With Color Coded Cap. |
| Weight per unit | 0.0600 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

## Features

| | |
|---|---|
| Material | Aluminum |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

## Material, Color, and Finish

| | |
|---|---|
| Color | OLIVE |
| Finish | Tin Plated Bronze |

## Dimensions and Weight

| | |
|---|---|
| Size | L=2.62 - OD=.689 - ID=.440 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
10524 W US Hwy 80
75126-0000, TX Forney
Phone: 972-210-2783
Fax: 972-210-2784

## Descriptions

| | |
|---|---|
| Description | 2/0 AL/CU COMPRESSION BUTT SPLICE |
| extra long description | NSI ASC2/0T 2/0 Awg Alum Compressio |
| Features | Dual Rated Aluminum Splice 2/0 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap. |
| Long Description | Dual Rated Aluminum Splice 2/0 AWG Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap. |
| Product Type | 2/0 Awg Alum Compression Splice(Al/Cu) |
| Special Features | 2/0 AWG (STR) - ALCU Splice |

## Manufacturer Information

| | |
|---|---|
| Brand | Nsi Industries |
| GTIN | 00662381032058 |
| Manufacturers Part Number | ASC2/0T |
| UPC | 662381032058 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Standard Barrel - ALCU Splice |

## Packaging

| | |
|---|---|
| Carton | 12 |
| Weight Per each | 0.06 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| standard | UL486A/B |
| Temperature Rating | 90 C |