



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ASC750T #750 Alum Comp SPLC *Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | ASC750T  |
| Manufacturer     | Nsi Industries   |
| Description      | Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices Are A Type Of Aluminum Compression Connector That Is Produced From High Conductivity Aluminum Tubing. Center Stop Assures Proper Cable Installation. Electro-Tin Plated For Corrosion Resistance. Color Coded and Marked With Die Index Information. Pre-Filled With Oxide Inhibitor and Capped With Color Coded Cap. |
| Weight per unit  | 0.7000 (lbs/each)  |
| Product Category | Splicing & Terminating Kits  |

### Features

|                      |          |
|----------------------|----------|
| Material             | Aluminum |
| Number of Conductors | 2        |
| Poles                | 1        |
| Voltage Rating       | 600 V    |
| Warranty             | 1 YEAR   |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Color  | Yellow     |
| Finish | Tin Plated |

### Dimensions and Weight

|      |                            |
|------|----------------------------|
| Size | L=5.37 - OD=1.60 - ID=1.02 |
|------|----------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | #750 ALUM COMP SPLC  |
| extra long description | NSI ASC750T 750 Mcm Alum Compressio  |
| Features               | Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap. |
| Long Description       | Dual Rated Aluminum Splice 750 MCM Dual Rated Aluminum Splices are a type of aluminum compression connector that is produced from high conductivity aluminum tubing. Center stop assures proper cable installation. Electro-tin plated for corrosion resistance. Color coded and marked with die index information. Pre-filled with oxide inhibitor and capped with color coded cap. |
| Product Type           | 750 MCM Alum Compression Splice(Al/Cu)   |
| Special Features       | 750 MCM (STR) - ALCU Splice  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Polaris        |
| GTIN                      | 00662381032140 |
| Manufacturers Part Number | ASC750T        |
| UPC                       | 662381032140   |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Standard Barrel - ALCU Splice     |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 3   |
| Weight Per each | 0.7 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C                                    |
| standard                 | UL486A/B                                |
| Temperature Rating       | 90 C                                    |