Ariadni LED+ Dimmer

Dimmer for LED, CFL, Halogen and Incandescent dimmable bulbs.

Features

- On/off toggle switch with a captive linear-slide dimmer for a traditional wallplate opening
- Advanced dimming technology designed for compatibility with a broad range of high-efficacy bulbs.
- UL Listed to control:
 - Dimmable LED with integrated driver
 - Halogen
 - Incandescent
 - Dimmable compact fluorescent load (CFL) with integrated ballast
- Low-end adjustment to accommodate a wide range of bulbs
- 100% factory tested
- Formerly C•L

Application Requirements

- When dimming CFLs or LEDs, only bulbs marked or rated as DIMMABLE may be used.
- For a complete list of compatible DIMMABLE LEDs please visit www.lutron.com/dimcflled. For questions call 1.800.523.9466.

Model Numbers

AYCL-153P-XX^{1,2} Single pole/3-way³ AYCL-153PH-XX-C⁴ Single pole/3-way³

- ² For clamshell packaging, add "H" after "153P".
- ³ For 3-way and 4-way switching, use Claro switches or other mechanical switches.
- ⁴ Clamshell packaged product for Canada.



369686d 1 07.09.20

* Wallplate sold separately

LUTRON SPECIFICATION SUBMITTAL

Job Number:

Model Numbers:

[&]quot;XX" in the model number represents color/finish code; see "Colors and Finishes" chart on next page.

Specifications

Regulatory Approvals

- UL Listed to US and Canadian safety requirements UL1472 / CSA C22.2 184.1
- NOM

Power and Ratings

- 120 V∼ 60 Hz
- 150 W dimmable LED/CFL

or

• 600 W Incandescent/Halogen

or

Mixed bulb type per Multigang and Mixed Bulb
 Type Ratings table (see page 3)

Environment

- For indoor use only.
- Operating temperatures 0 °C to 40 °C (32 °F to 104 °F).

Performance

- Power-failure memory
- Captive linear slider
- Electrostatic discharge tested
- Precise color matching
- Mechanical air-gap switch to disconnect load power

Warranty

• 1 Year Limited Warranty

For additional Warranty information, please visit www.lutron.com/TechnicalDocumentLibrary/ 369-119_Wallbox_Warranty.pdf

2.58 in (66 mm) 2.86 in (73 mm) (30 mm)

369686d 2 07.09.20

Colors and Finishes

Gloss Finishes

Add color/finish code to model #

Example: AYCL-153P-WH

WH White
IV Ivory
AL Almond
LA Light Almond

BR Brown BL Black

STUTRON SPECIFICATION SUBMITTAL

源LO II (OI)	3F LOTI TOATTO	1 SODIVITIAL	raye
Job Name:		Model Numbers:	
Job Number:			


369686d 3 07.09.20

Multigang and Mixed-Bulb-Type Ratings

When installing more than one Dimmer in the same wallbox, it may be necessary to remove some side sections prior to wiring (see diagram). Removal of Dimmer side sections may reduce maximum wattage, as shown in the chart below.

Mixing bulb types (using a combination of LED/CFL, and Incandescent/Halogen bulbs) will also affect the maximum ratings, as shown in the chart below.

*EXAMPLE: If one set of side sections is removed and you have three 10 W LEDs bulbs installed (Total LED Wattage = 30 W), you may add up to 300 W of incandescent or halogen lighting.




Total CFL/LED Wattage Installed (Wattage per bulb x # of bulbs)		Maximum Allowable Incandescent/Halogen Wattage		
		No sides removed	1 side removed	2 sides removed
0 W	+	600 W	500 W	400 W
1 W – 25 W	+	500 W	400 W	300 W
26 W – 50 W	+	400 W	300 W	200 W
51 W – 75 W	+	300 W	200 W	100 W
76 W – 100 W	+	200 W	100 W	50 W
101 W – 125 W	+	100 W	50 W	0 W
126 W – 150 W	+	0 W	0 W	0 W


LUTRON SPECIFICATION SUBMITTAL


Job Name:	Model Numbers:
Job Number:	

369686d 4 07.09.20


Operation (View with wallplate removed)








Lever-type Adjustment Dial



OR

Wheel-type Adjustment Dial




LUTRON SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	


369686d 5 07.09.20

Wiring Diagrams


Single-Pole Wiring



3-Way Wiring



4-Way Wiring



- or Copper/Black screw terminal
- ** or Brass/Gold screw terminal
- *** or Green screw terminal
- † Please refer to switch instruction sheet for proper wiring.

Note for 4-Way Wiring:

Dimmer must be installed Line Side or Load Side. It cannot be installed in the 4-way location.

LUTRON SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:	
l		
Job Number:		