



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4281 Crawford Dr.
79602, TX Abilene
Phone: 325-793-1570
Fax: 325-692-9649



AYLV600PWH Ariadni 450W Magnetic Low Voltage SP White

Lutron

| | |
|------------------|---|
| Catalog Number | AYLV600PWH |
| Manufacturer | Lutron |
| Description | Ariadni Dimmer, Magnetic Low-Voltage, Single-Pole, Preset, 120V/600VA (450W) In White |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|----------------|
| actuator | Toggle Switch |
| connection | Screw Terminal |
| Connection Type | Screw Terminal |
| insulation | Plastic |
| Material | Plastic/Metal |
| media | Yes |
| Poles | 1 |
| Switch Type | Toggle |
| Voltage Rating | 120 |
| Wattage | 450 |

Material, Color, and Finish

| | |
|--------|-------|
| Color | White |
| Finish | Gloss |

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.60 x 2.86;117 x 73 |
|------|----------------------|

Descriptions

| | |
|------------------------|---|
| Description | ARIADNI 450W MAGNETIC LOW VOLTAGE SP WHITE |
| extra long description | LUT AYLV-600P-WH ARIADNI 600VA PRES |
| Long Description | Ariadni Dimmer, Magnetic Low-Voltage, Single-pole, preset, 120V/600VA (450W) in white |
| Product Type | Ariadni 600VA Preset White |
| Special Features | Controls 600 VA (450 W) magnetic low-voltage loads. Toggle turn lights on/off. Slide up to brighten, down to dim. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Lutron |
| GTIN | 00027557687294 |
| Manufacturers Part Number | AYLV-600P-WH |
| UPC | 027557687294 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4281 Crawford Dr.
79602, TX Abilene
Phone: 325-793-1570
Fax: 325-692-9649

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Preset dimmer, single-pole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.25 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | Indoor use only |
| Frequency Rating | 50 to 60 |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, cUL |