


# ROTOMATIC RM-202AA

BX, MC & Flex  
Motorized  
Bench Top Cutter



Automatically strip the end  
of armored flexible cable!



U.S. Patents  
4,103,578 & 4,169,400  
other Patents Pending

Cuts 3/8" Flex  
(0.54 Maximum Cable O.D.)

The heavy-duty Rotomatics are the culmination of years of experience in armored cable cutting technology and are used in production lines of major armored cable manufacturers

SEATEK COMPANY'S PEGBOARD  
DISPLAYSHOWCASE UNIQUE TOOLS  
& INCREASE SALES



## ACCESSORIES FOR SEATEK TOOLS

ITEM	CAT. NO.	SPECIFICATIONS	ITEM	CAT. NO.	SPECIFICATIONS
 ROTO-SPLIT & ROTO-FLEX	B-102	BLUE SAPPHIRE BLADE. REPLACEMENT BLADE FOR USE ON BX & FLEX CUTTERS: RS-101, RS-101A, RF-120A, RF-120B AND RF-170. (NOT RECOMMENDED TO CUT ALUMINUM ARMOR)	 HANDLE ASSEMBLY	101-110	HANDLE ASSEMBLY FOR RS-101, RS-101A, RF-120A, RF-120B AND RF-170 WITH BLADE CARTRIDGE STORED IN KNOB. (BLADE NOT INCLUDED)
 ALUMINUM ARMOR	B-107	BLADE TO CUT ALUMINUM ARMOR. FOR USE ON BX & FLEX CUTTERS: RS-101, RS-101A, RF-120A, RF-120B AND RF-170 (WORKS ON STEEL CASING TOO BUT ONLY FOR 1/2" TRADE SIZE & ABOVE).	 HARDWARE RETROFIT	101-106	SPARE PART KIT FOR RS-101, RS-101A, RF-120A, RF-120B & RF-170. CONSISTING OF 1 SHAFT, 1 NUT, 1 4-40 KNURLED SCREW, 1 THUMBSCREW FOR RS-101 ONLY.
 ROTOMATIC	B-103	FINE TOOTH BLADE USED ON POWER TOOLS TO CUT THIN WALL FLEX	 POWER CONVERSION	101-107	POWER CONVERSION KIT. MOTORIZE ANY ROTO-SPLIT AND ROTO-FLEX (SAME PRINCIPLE AS POWER-SPLIT). CONSISTS OF B-108 BLADE, SHAFT, SCREW, WASHERS, HEX NUT & HEX WRENCH.
	B-108	STANDARD BLADE FOR RM-202 (ALL MODELS). ALSO USE WITH RS-101-AP.			
 ROTO-SKINNER	B-151	REPLACEMENT BLADE FOR RSK-145, RSK-150 & RSK-150RC ROTO-SKINNER	 SWING-SAW	B-109-18	REPLACEMENT BLADES FOR SW-130 SWING-SAW. USE 18 TEETH PER INCH FOR THICKER WALL EMT, AND 24 TEETH PER INCH FOR THIN WALL LIQUID TIGHT, FLEX, ETC..
	B-153	REPLACEMENT BLADE FOR RSK-125 ROTO-SKINNER	 REPLACEMENT BLADE	B-109-24	
 LUBRICANT STICK	LS-105	LUBRICANT STICK FOR BLADES USED ON RS-101, RS-101A, RS-101AP, RF-120A, RF-120B & RF-170. <b>NOT FOR USE WHEN CUTTING ALUMINUM ARMOR.</b>	 JACKET RIPPER	B-228	REPLACEMENT BLADE FOR JACKET RIPPER JR-128.
 REPLACEMENT BLADE	B-252	REPLACEMENT BLADE FOR CT-250 ROTO-SPIN®.	 STRIP-ALL	B-202	REPLACEMENT BLADE FOR ALL MODELS OF THE SA-200 STRIP-ALL. SOLD IN PACKAGES OF TWO.
	B-272	REPLACEMENT BLADE FOR VT-270 VEE-TWIN.			
 ZIP-STRIPPER REPLACEMENT BLADE	BZ-112	REPLACEMENT BLADE FOR UF CABLE STRIPPER ZIP-STRIPPER ZS-140	 STRIP-ALL ADAPTER	A-201	A-201 ADAPTER USED TO STRIP AND RING CUT WIRES AS SMALL AS 1/8". GREAT FOR USE ON COMMUNICATIONS AND COAX CABLE. FOR ALL MODELS OF THE SA-200 STRIP-ALL. (EXCEPT SA-200L)

Distributed By:




A SMALL COMPANY WITH BIG IDEAS®

392 PACIFIC STREET, STAMFORD, CT 06902

PHONE (203) 324-0067 ☆ FAX (203) 324-7844 ☆ E-Mail: info@SeatekCo.com

www.SeatekCo.com




# ROTOMATIC RM-202AA

BX, MC & Flex  
Motorized  
Bench Top Cutter



Automatically strip the end  
of armored flexible cable!



U.S. Patents  
4,103,578 & 4,169,400  
other Patents Pending

















Cuts 3/8" Flex  
(0.54 Maximum Cable O.D.)

The heavy-duty Rotomatics are the culmination of years of experience in armored cable cutting technology and are used in production lines of major armored cable manufacturers

SEATEK COMPANY'S PEGBOARD  
DISPLAYSHOWCASE UNIQUE TOOLS  
& INCREASE SALES



## ACCESSORIES FOR SEATEK TOOLS

ITEM	CAT. NO.	SPECIFICATIONS	ITEM	CAT. NO.	SPECIFICATIONS
 ROTO-SPLIT & ROTO-FLEX	B-102	BLUE SAPPHIRE BLADE. REPLACEMENT BLADE FOR USE ON BX & FLEX CUTTERS: RS-101, RS-101A, RF-120A, RF-120B AND RF-170. (NOT RECOMMENDED TO CUT ALUMINUM ARMOR)	 HANDLE ASSEMBLY	101-110	HANDLE ASSEMBLY FOR RS-101, RS-101A, RF-120A, RF-120B AND RF-170 WITH BLADE CARTRIDGE STORED IN KNOB. (BLADE NOT INCLUDED)
 ALUMINUM ARMOR	B-107	BLADE TO CUT ALUMINUM ARMOR. FOR USE ON BX & FLEX CUTTERS: RS-101, RS-101A, RF-120A, RF-120B AND RF-170 (WORKS ON STEEL CASING TOO BUT ONLY FOR 1/2" TRADE SIZE & ABOVE).	 HARDWARE RETROFIT	101-106	SPARE PART KIT FOR RS-101, RS-101A, RF-120A, RF-120B & RF-170. CONSISTING OF 1 SHAFT, 1 NUT, 1 4-40 KNURLED SCREW, 1 THUMBSCREW FOR RS-101 ONLY.
 ROTOMATIC	B-103	FINE TOOTH BLADE USED ON POWER TOOLS TO CUT THIN WALL FLEX	 POWER CONVERSION	101-107	POWER CONVERSION KIT. MOTORIZE ANY ROTO-SPLIT AND ROTO-FLEX (SAME PRINCIPLE AS POWER-SPLIT). CONSISTS OF B-108 BLADE, SHAFT, SCREW, WASHERS, HEX NUT & HEX WRENCH.
	B-108	STANDARD BLADE FOR RM-202 (ALL MODELS). ALSO USE WITH RS-101-AP.			
 ROTO-SKINNER	B-151	REPLACEMENT BLADE FOR RSK-145, RSK-150 & RSK-150RC	 SWING-SAW	B-109-18	REPLACEMENT BLADES FOR SW-130 SWING-SAW. USE 18 TEETH PER INCH FOR THICKER WALL EMT, AND 24 TEETH PER INCH FOR THIN WALL LIQUID TIGHT, FLEX, ETC..
	B-153	REPLACEMENT BLADE FOR RSK-125	 REPLACEMENT BLADE	B-109-24	
 LUBRICANT STICK	LS-105	LUBRICANT STICK FOR BLADES USED ON RS-101, RS-101A, RS-101AP, RF-120A, RF-120B & RF-170. <b>NOT FOR USE WHEN CUTTING ALUMINUM ARMOR.</b>	 JACKET RIPPER	B-228	REPLACEMENT BLADE FOR JACKET RIPPER JR-128.
 ROTO-SPIN	B-252	REPLACEMENT BLADE FOR CT-250	 STRIP-ALL	B-202	REPLACEMENT BLADE FOR ALL MODELS OF THE SA-200 STRIP-ALL. SOLD IN PACKAGES OF TWO.
 VEE-TWIN	B-272	REPLACEMENT BLADE FOR VT-270			
 ZIP-STRIPPER REPLACEMENT BLADE	BZ-112	REPLACEMENT BLADE FOR UF CABLE STRIPPER ZIP-STRIPPER ZS-140	 STRIP-ALL ADAPTER	A-201	A-201 ADAPTER USED TO STRIP AND RING CUT WIRES AS SMALL AS 1/8". GREAT FOR USE ON COMMUNICATIONS AND COAX CABLE. FOR ALL MODELS OF THE SA-200 STRIP-ALL. (EXCEPT SA-200L)

**Distributed By:**



A SMALL COMPANY WITH BIG IDEAS®

392 PACIFIC STREET, STAMFORD, CT 06902

PHONE (203) 324-0067 ☆ FAX (203) 324-7844 ☆ E-Mail: info@SeatekCo.com

www.SeatekCo.com

