



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101  
85297-0000, AZ Gilbert  
Phone: 602-325-9757  
Fax: 602-325-9758



## B2011PAZN BLTF 1-1/4" Pa Zinc Plate Rigid Pipe Clamp

*Cooper B-Line/Cable Tray*

Catalog Number	B2011PAZN
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Pre-Assembled O.D. Pipe and Conduit Clamp, 0.0705" H X 3.3510" L X 1.25" W, Steel
Weight per unit	0.2000 (lbs/each)
Product Category	Channel & Strut Fittings

### Features

dimensions	3.3510 IN X 1.2500 IN X 0.0705 IN
Material	14 Gauge Low Carbon Steel

### Material, Color, and Finish

Finish	Zinc Plated
--------	-------------

### Dimensions and Weight

Size	1-1/4 in
------	----------

### Descriptions

Construction	TWO PIECE
Description	BLTF 1-1/4" PA ZINC PLATE RIGID PIPE CLAMP
extra long description	B-LINE B2011PAZN 1 1/4" PIPE/CONDUIT
Features	Eaton offers a wide variety of B-Line series pipe clamps and accessories used for the support and attachment of pipe to structural members.
Long Description	Eaton B-Line series pre-assembled O.D. pipe and conduit clamp, 0.0705" H x 3.3510" L x 1.25" W, Steel
Product Type	1 1/4" Pipe/Conduit Clamp, Pre-Asm, Rigid, 1 1/4", ZN PLTD
Special Features	Includes Combination Recess Hex Head Machine Screw and Square Nut

### Manufacturer Information

Brand	Eaton
GTIN	00781011610449
Manufacturers Part Number	B2011PAZN
UPC	781011610449

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	Pre-assembled O.D. pipe and conduit clamp

### Packaging

Carton	1
Package	50
Weight Per each	0.2



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

425 East Germann Road Suite 101  
85297-0000, AZ Gilbert  
Phone: 602-325-9757  
Fax: 602-325-9758

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting	CHANNEL
standard	Not Applicable